







ebm-papst MFG. NOTES

SEE SHEET 1 FOR REVISION HISTORY

I N/A

Ø 11 [.43]
8 PLACES

580 [22.83]

530 [20.87]

630 [24.80]

355,4 [13.99]

314,07 [12.365]

5,3 [.21]
REF.

ebm-papst Inc. DISCLOSURE		MATERIAL:		BEND DEDUCTION		PART NO. EGIR-240-500-30	
THIS DOCUMENT IS THE PROPERTY OF ebm-papst Inc. ITS USE IS AUTHORIZED BY ebm-papst Inc. ONLY. ALL QUESTIONS MUST BE REFERRED TO ebm-papst Inc. PERSONNEL: DESIGN ENG., MFG. ENG., AND / OR PURCHASING.		FINISH: SEE SHEET 1		COSMETICS PER ebm-papst SPEC-Q-1		TITLE EGIR-240-500-30 ASSEMBLY	
IF APPLICABLE, ENTER SECOND FINISH AND DESCRIPTION HERE		SEE CAD FOR DIMS. NOT SHOWN		BREAK ALL SHARP EDGES		FIRST USED ON	
ALL INNER BEND RADII = 1mm BOTTOM BEND UNLESS OTHERWISE STATED		TOLERANCES, UNLESS OTHERWISE STATED:		ALL DIMENSIONS ARE IN INCHES			
DECIMAL .xxx ± .020 HOLES .xxx ± .003		TOLERANCES FOR CNC FLAT .xxx		TOLERANCES FOR EXCLUDING HOLE DIA. +/- .010		DESIGN ENG. JLL	
TOLERANCE .xx ± .030 ANGLES ± 1° REF						ORIG. DATE 12-Apr-13	
						E# ELECT.	
Form No. 1073 Rev. H						REVISION 001	
						SHEET 2 of 2	