

1		2		3		4											
<table border="1"> <tr> <th>Part No.</th> <th>Cable color</th> </tr> <tr> <td>~04*1TV~</td> <td>WHITE</td> </tr> <tr> <td>~04*2TV~</td> <td>BLACK</td> </tr> </table>								Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK				
Part No.	Cable color																
~04*1TV~	WHITE																
~04*2TV~	BLACK																
NOTE ① We indicate the length of the harness on the last of product name, 'L' part. ② Tolerance for [L] <table border="1"> <tr> <th>Length L [mm]</th> <th>Tolerance [mm]</th> </tr> <tr> <td>$35 \leq L \leq 200$</td> <td>± 4</td> </tr> <tr> <td>$200 < L \leq 500$</td> <td>± 8</td> </tr> <tr> <td>$500 < L \leq 1000$</td> <td>± 12</td> </tr> <tr> <td>$1000 < L$</td> <td>$\pm 1.5\%$</td> </tr> </table> ③ Connector rotation angle is within ± 45 degree from the above image. For long length in the case of $L > 500$, the angle is optional. 4. Specifications are subject to change without notice.								Length L [mm]	Tolerance [mm]	$35 \leq L \leq 200$	± 4	$200 < L \leq 500$	± 8	$500 < L \leq 1000$	± 12	$1000 < L$	$\pm 1.5\%$
Length L [mm]	Tolerance [mm]																
$35 \leq L \leq 200$	± 4																
$200 < L \leq 500$	± 8																
$500 < L \leq 1000$	± 12																
$1000 < L$	$\pm 1.5\%$																
【 DIMENSIONS OF CONNECTOR 】																	
1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable	HALOGEN FREE												
NO.	PART NO.	CODE NO.	NO.	PART NO.													
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED										
		APPROVED : TS. NOBE 18.06.18 CHECKED : MT. KANEKO 18.06.18 DESIGNED : MS. MATSUMOTO 18.06.18 DRAWN : MS. MATSUMOTO 18.06.18		DRAWING NO. U.FL-2LPHF6-04**TV-A-L ① PART NO. ① CODE NO. ①													