







DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012



- NOTE
- 1 REFERENCE IS A.
 - 2 LEAD CO-PLANARITY SHALL BE 0.1 MAX .
 - 3 THICKNESS OF SUPPORTING TAPE SHALL BE $0.188(7.5\text{mil}) \text{ MIN}$.
 - 4 THIS PRODUCT SATISFIES HALOGEN FREE REQUIREMENTS DEFINED AS 900 PPM MAXIMUM CHLORINE, 900 PPM MAXIMUM BROMINE, AND 1500 PPM MAXIMUM TOTAL OF CHLORINE AND BROMINE.

5	BRASS	TIN PLATING 1#MMIN OVER NICKEL 1#MMIN	10	(CONNECTOR)				
4	BRASS	TIN PLATING 1#MMIN OVER NICKEL 1#MMIN	9	POLYSTYRENE				
3	PHOSPHOR BRONZE	GOLD PLATING 0.05#MMIN OVER NICKEL 1#MMIN	8	POLYESTER				
2	LCP	(BLACK) UL94V-0	7	POLYSTYRENE				
1	LCP	(GRAY) UL94V-0	6	POLYIMIDE				
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 5 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.	APPROVED : NM. NISHIMATSU		10.08.05		DRAWING NO. EDC3-159698-03			
	CHECED : HS. SAKAMOTO		10.08.05		PART NO. FH28-10S-0.5SH(11)			
	DESIGNED : TO. SHIBUYA		10.08.04		CODE NO. CL586-1861-4-11			
	DRAWN : TO. SHIBUYA		10.08.04		 1/2			

DRAWING FOR REFERENCE: This is subject to change without notice
08/11/2012

