

Intel® Desktop Board DZ77RE-75K



ATX Form Factor

Best Intel® Desktop Board
for The Intel® -K Processors



PRODUCT BRIEF

Extreme Series



Intel® Desktop Board DZ77RE-75K



Optimized for Intel® -K Processors!

Introducing the Intel® Desktop Board DZ77RE-75K. Intel®'s first Desktop Board with Thunderbolt Technology. Also optimized for Intel® -K processors to maximize your overclocking performance.

Build Upon a Winner

The first Intel® Desktop Board with Thunderbolt Technology, DZ77RE-75K offers revolutionary I/O Technology targeted for performance and flexibility in system design. Thunderbolt technology offers a 10Gb/s bi-directional interface with dual protocol for both data and display. Daisy chaining multiple devices through one individual connection to the PC allows for simplicity and flexibility in system design. Also BEST in a series of newly introduced -K Intel® Desktop Boards, the DZ77RE-75K is highly optimized to take full advantage of the Intel® -K processors. Combination of very sophisticated system hardware design and ease of performance tuning and overclocking of the Core, Graphics, and memory offered by the Intel® Visual BIOS make the DZ77RE-75K our BEST board for the Intel® -K processors. Intel® -K Series Desktop Board PLUS Intel® -K processor EQUALS performance.

INTEL® VISUAL BIOS Advanced Overclocking

The new Intel® Visual BIOS offers graphical interface and animated controls which allow you to configure settings faster and take full advantage of your Intel® -K processors. Also, included within the Intel® Visual BIOS, the Intel® Overclocking Assistant¹ provides single-step overclocking boosts to quickly maximize your gaming advantage. This is a very user-friendly feature which allows easy overclocking of Core, Graphics, and Memory. Intel Visual BIOS operates by your choice of touch screen, keys,

or mouse. All controls are literally at your fingertips, in a format you can visualize. When your quest for ultimate performance takes you to extremes, choose the Intel® Desktop Board DZ77RE-75K and Intel® Visual BIOS.

Power and Responsiveness for the Hottest New Games

The advanced power and overclocking¹ capabilities of the DZ77RE-75K board coupled with the dramatic responsiveness improvements delivered by the Intel® Smart Response Technology provide the board of choice for gamers and media creation enthusiasts alike. Intel Smart Response Technology provides SSD like performance and up to 50% improvement in responsiveness as compared to an HDD only system². The Intel® Desktop Board DZ77RE-75K also includes other new responsiveness technologies such as Intel® Rapid Start Technology³ which allow the user to quickly resume the system from sleep and standby modes.



Extreme Series

The Boxed Intel® Desktop Board DZ77RE-75K Solution Includes:

- Intel® Desktop Board DZ77RE-75K
- ATX 2.2 compliant I/O shield
- UV reactive SATA cables
- Extreme mouse pad
- Bluetooth®*/Wi-Fi module
- Front Panel USB*
- Board and back panel I/O layout stickers
- Quick reference guide
- Intel® Express Installer driver and software DVD
- Windows® Premium WHQL certified
- NVIDIA® SLI® Bridge connectors
- Post code information card



INCLUDES: Front Panel USB 3.0 module included on Boxed version of DZ77RE-75K




Bluetooth® 2.1/Wi-Fi-802.11b/g/n module

SOFTWARE FOR INCREASED PERFORMANCE

Security	Protect against antivirus threats with industry-leading solutions from McAfee® and ESET® Smart Security.
Gaming	Unlock your gaming potential with Razer® peripherals and Steam® online games.
GPU Virtualization	Lucid Virtu® Universal adds to existing multi GPU capabilities by eliminating tearing effects in games if frame rates are increased beyond monitor's refresh rate.
Utilities	Increase productivity with Splashtop® Remote Desktop and LapLink® PCmover. Customize BIOS and monitor PC Health with Intel® Visual BIOS and Intel® Desktop Utility.

Intel® Desktop Board DZ77RE-75K

Features and Benefits



Extreme Series

- Support for the Intel® Core™ i7 processor in the LGA1155 package.** Highly optimized for the Intel® -K Processors. Features Intel® Turbo Boost Technology⁴, Intel® Hyper-Threading Technology⁵ for exceptional performance and scalability, and 8 MB Shared Intel® Smart Cache, enabling dynamic and efficient allocation of cache.
- Intel® Z77 Express Chipset:** Features Intel® Smart Response Technology.
- Thunderbolt connector** providing revolutionary I/O technology with 10Gb/s bi-directional dual protocol interface for data and display.
- Four DIMM slots:** Designed to support overclocked¹ DDR3 2400MHz+ O.C.⁶ memory, delivering up to 32 GB/s memory bandwidth.
- Eight Super-Speed USB 3.0 ports (4 external, 4 via internal header), two IEEE 1394a ports (1 external, 1 via internal header), and 10 USB 2.0 ports (4 External, 6 via internal headers):** Two USB 2.0 ports provide high current and fast charging capability.
- Two PCI Express 3.0* × 16 slots:** Ability to scale to dual ×8 graphics support for certified AMD CrossFireX* and NVIDIA* SLI.*
- PCI Express* and PCI connectors:** Flexibility to support PCI Express and legacy PCI devices.
- Four SATA 6.0 Gb/s ports, four SATA 3.0 Gb/s ports, and one eSATA 6.0 Gb/s.**
- Intel® Rapid Storage Technology:** Performance and reliability with support for RAID 0, 1, 5, 10, and Intel® Rapid Recover Technology.
- Intel® Smart Response and Intel® Rapid Start³ Technologies:** Provides SSD like performance with HDD capacity. Dramatically improves response time when a small capacity SSD is used in conjunction with a large HDD.
- (8+2) 10-channel Intel® High Definition Audio⁷ (7.1):** Enables high-quality integrated audio that rivals the performance of high-end discrete solutions.
- Dual Intel® Gigabit Ethernet LAN:** Features onboard 10/100/1000 Mb/s Ethernet LAN connectivity.
- Consumer infrared receiver and transmitter:** Supports receiving, learning, and emitting capabilities, controls up to two additional CE devices with your PC, and eliminates the need for a USB CIR dongle.
- Back-to-BIOS switch:** Allows easy access to the BIOS for easy overclocking¹ and recovery.
- Post code decoder:** Allows for display of post codes for debug along with the included post code quick reference card displaying critical areas to help troubleshoot performance-increase roadblocks.
- Initialization and diagnostic LEDs:** Provides instant visible system feedback.
- Exclusive voltage regulator heat sinks:** Provides reliable and silent cooling for extreme Core, Graphics, and Memory performance tuning.
- 100% Solid state capacitors and exclusive Power Supervisor:** Maximizes stability and power for advanced performance tuning.
- Tweaker switches:** Power and reset switches for quick reset, and power on.
- ATX (9.6" × 11.6") Form Factor:** ATX board supports more fully featured tower designs.
- Lead-free:** Meets all worldwide regulatory requirements for lead-free manufacturing.

Intel® Desktop Board DZ77RE-75K

Technical Specifications

PROCESSOR

Processor Support

- Highly Optimized for Intel® -K Processors
- Intel® Core™ i7 processors in the LGA1155 package
- Intel® Turbo Boost Technology⁵
- Intel® Hyper-Threading Technology⁶
- Integrated Memory Controller with support for up to 32 GB⁷ of system memory DDR3 2400MHz + O.C. SDRAM
- Intel® Fast Memory Access
- Supports Intel® 64 architecture⁸

CHIPSET

Intel® Z77 Express Chipset

- Intel® Z77 PCH
- Intel® Rapid Storage Manager (RAID 0, 1, 5, 10)
- Intel® Smart Response Technology
- Intel® Rapid Start Technology³
- Four SATA (6.0 Gb/s), four SATA (3.0 Gb/s) ports and one eSATA (6.0 Gb/s)

THUNDERBOLT CONNECTOR

- 10Gb/s bi-directional and dual protocol for data and display

USB PORTS

- Four Hi-Speed USB 2.0 ports via back panel, including two fast charging high current ports (yellow)
- Six additional Hi-Speed USB 2.0 ports via four internal headers
- Four Super-Speed USB 3.0 ports (blue) and four Super-Speed USB 3.0 via internal headers

SYSTEM BIOS

- 32 Mb Flash EEPROM with Intel® Platform Innovation Framework for EFI Plug and Play, IDE drive auto-configure
- Advanced configuration and power interface V3.0b, DMI 2.5

FAST BOOT

- Fast Boot
- Intel® Express BIOS update support: BIOS update via F7 function key

HARDWARE MANAGEMENT FEATURES

- Processor fan speed control
- System chassis fan speed control
- Voltage and temperature sensing
- Fan sensor inputs used to monitor fan activity
- Power management support for ACPI 3.0b

INTEL® PRO 10/100/1000 NETWORK CONNECTION

- Dual Intel® LAN on the back panel
- New low-power design can meet Energy Star® 5.0 specifications

EXPANSION CAPABILITIES

- Two PCI Express® 3.0 ×16 connectors (configured as ×8/×8 in dual graphics mode)
- Two PCI Express 2.0 ×1 slots
- Two PCI slots

AUDIO

- 10-channel Intel® High Definition Audio⁹ codec
- 8-channel via the back panel
- 2-channel via the front panel
- Back panel support for output via optical cable
- One internal header for S/PDIF output for HDMI* support

SYSTEM MEMORY

Memory Capacity

- Four 240-pin DIMM connectors supporting dual-channel memory. Two double-sided DIMMs per channel
- Maximum system memory up to 32 GB¹⁰ using 8 GB double-sided DIMMs

Memory Types

- DDR3 1600+ O.C. SDRAM memory support
- Non-ECC Memory

Memory Voltage

- 1.35 V low voltage
- 1.5 V standard JEDEC voltage
- Support for Intel® XMP extended voltage profiles

JUMPERS AND FRONT PANEL CONNECTORS

Jumpers

- Single configuration jumper design
- Jumper access for BIOS maintenance mode

Front Panel Connectors

- Reset, HD LED, Power LEDs, power on/off
- Four front-panel Hi-Speed USB 2.0 headers
- One front-panel Super-Speed USB 3.0 headers
- Front-panel audio header
- One IEEE 1394a header

MECHANICAL

Board Style

- ATX

Board Size

- 11.6" × 9.6" (29.46 cm × 24.38 cm)

Baseboard Power Requirements

- ATX 12 V

ENVIRONMENT

Operating Temperature

- 0°C to +55°C

Storage Temperature

- 20°C to +70°C

REGULATIONS AND SAFETY STANDARDS

United States and Canada

- UL 1950, Third edition - CAN/CSA C22.2 No. 950-95 with recognized U.S. and Canadian component marks

Europe

- Nemko certified to EN 60950 International
- Nemko certified to IEC 60950 (CB report with CB certificate)

EMC REGULATIONS

(tested in representative chassis)

United States

- FCC Part 15, Class B
- FCC Part 15, Class B open-chassis (cover off) testing

Canada

- ICES-003, Class B

Europe

- EMC directive 89/336/EEC; EN 55022:1998 Class B; EN 55024:1998

Australia/New Zealand

- AS/NZS 3548, Class B

Taiwan

- CNS 13438, Class B International
- CISPR 22:1997, Class B

Environmental Compliance


Complies with US CRF via EN55022 +6 db in system configurations with an open chassis and EU Directive 89/336/EEC and use via EN55022 and EN50082-1 in a representative chassis. Lead-Free: The symbol is used to identify electrical and electronic assemblies and components in which the lead (Pb) concentration level in any of the raw materials and the end product is not greater than 0.1% by weight (1000 ppm). This symbol is also used to indicate conformance to lead-free requirements and definitions adopted under the European Union's Restriction on Hazardous Substances (RoHS) directive, 2002/95/EC.

For ordering information, visit

www.intel.com

For the most current product information, visit

www.intel.com/go/idb



1 Warning: Altering clock frequency and/or voltage may (i) reduce system stability and useful life of the system and processor, (ii) cause the processor and other system components to fail, (iii) cause reductions in system performance, (iv) cause additional damage, and (v) affect system data integrity. Intel has not tested, and does not warrant, the operation of the processor beyond its specifications.

2 Responsive performance measurements performed using Intel Core Processor, Intel Z68 Express Chipset, Intel® Solid-State Drive, and Intel® Rapid Storage Technology driver. Performance as measured by PCMark Vantage v1.0.1 tests on systems with Intel DZ68BC motherboard, Intel Core processor, Intel 6 Series chipset, Microsoft Windows® 7 Ultimate 64-bit, SATA 2 for both SSD and HDD, Hitachi 7200 RPM 320 GB HDD, Intel 20/40/80 GB Solid-State Drives, Integrated Graphics, 4 GB 1066 MHz DDR 3 DRAM. System performance improvement on platforms is configuration-dependent; as measured by PCMark® Vantage tests. Boot times taken with Microsoft Velocity v4.3 and Microsoft PwrTest (included in Microsoft WDK, for 54 times only).

3 BIOS Update may be required to support Rapid Start Technology features. This feature may not be available at initial launch of product.

4 OC Assistant software and BIOS capability for this features may be available shortly after launch of product.

5 Intel® Turbo Boost Technology requires a PC with a processor with Intel Turbo Boost Technology capability. Intel Turbo Boost Technology performance varies depending on hardware, software, and overall system configuration. Check with your PC manufacturer on whether your system delivers Intel Turbo Boost Technology. See www.intel.com/technology/turboboost for more information.

6 Intel® Hyper-Threading Technology requires a computer system with a processor supporting HT Technology and an HT Technology-enabled chipset, BIOS, and operating system. Performance will vary depending on the specific hardware and operating system you use. For more information including details on which processors support HT Technology, see www.intel.com/info/hyperthreading.

7 Maximum peak memory bandwidth requires four DDR3 modules to be populated in each of the blue memory slots. DDR3 2400 memory support on this motherboard requires advanced knowledge of BIOS and memory tuning; individual results may vary. For specific supported memory for this motherboard, please visit www.intel.com/products/motherboard/ for more details.

8 64-bit computing on Intel® architecture requires a computer system with a processor, chipset, BIOS, operating system, device drivers, and applications enabled for Intel® 64 architecture. Processors will not operate (including 32-bit operation) without an Intel 64 architecture-enabled BIOS. Performance will vary depending on your hardware and software configurations. See <http://developer.intel.com/technology/intel64/index.htm> for more information.

9 Intel® High Definition Audio requires a system with an appropriate Intel® chipset and a motherboard with an appropriate codec and the necessary drivers installed. System sound quality will vary depending on actual implementation, controller, codec, drivers, and speakers. For more information about Intel® HD Audio, refer to www.intel.com/design/chipsets/ndaudio.htm.

10 System resources and hardware (such as PCI and PCI Express®) require physical memory address locations that can reduce available addressable system memory. This could result in a reduction of as much as 1 GB or more of physical addressable memory being available to the operating system and applications, depending on the system configuration and operating system.

INFORMATION IN THIS DOCUMENT IS PROVIDED IN CONNECTION WITH INTEL® PRODUCTS. NO LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE, TO ANY INTELLECTUAL PROPERTY RIGHTS IS GRANTED BY THIS DOCUMENT. EXCEPT AS PROVIDED IN INTEL'S TERMS AND CONDITIONS OF SALE FOR SUCH PRODUCTS, INTEL ASSUMES NO LIABILITY WHATSOEVER, AND INTEL DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY, RELATING TO SALE AND/OR USE OF INTEL PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT, OR OTHER INTELLECTUAL PROPERTY RIGHT.

Intel products are not intended for use in medical, life-saving, or life-sustaining applications. Intel may make changes to specifications and product descriptions at any time, without notice.

All products, dates, and figures specified are preliminary based on current expectations, and are subject to change without notice. Availability in different channels may vary.

Actual Intel® Desktop Board may differ from the image on the box.

*Other names and brands may be claimed as the property of others.

Copyright © 2012 Intel Corporation 05/12/FB/MED/PDF 327327-001US