APPROVAL SHEET

WLBD1608

Chip Bead

*Contents in this sheet are subject to change without prior notice.

FEATURES

1. Closed magnetic circuit.

APPLICATIONS

1. Noise reduction for general signal and DC line for General electronic circuits. Ex:PCs、Networking and Consumer electronics.

.

SHAPE and DIMENSION



Chip Size	
A	1.60±0.15
B	0.80±0.15
C	0.80±0.15
D	0.30±0.20

Units: mm

Ordering Information

WL	BD	1608	K1	U	300	T	B
Product Code WL: Inductor	**Series** BD: Chip Bead.	**Dimensions** 1.6 * 0.8 mm 1608 :EIA 0603	**Series extension** Refer to characteristic	**Tolerance** U: ±25%	**Value** 300 =30 OHM 301 =300 OHM 152 =1500 OHM	**Packing Code** T = 7" Paper Tape	B:STD

Electrical Characteristics

● WLBD1608 series

Walsin Part Number	Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA) max.
WLBD1608K1U300TB	30±25%	100	0.20	700
WLBD1608K1U600TB	60±25%	100	0.20	700
WLBD1608K1U800TB	80±25%	100	0.20	700
WLBD1608K1U121TB	120±25%	100	0.25	600
WLBD1608K1U151TB	150±25%	100	0.25	600
WLBD1608K1U221TB	220±25%	100	0.30	550
WLBD1608K1U301TB	300±25%	100	0.35	500
WLBD1608K1U471TB	470±25%	100	0.45	350
WLBD1608K1U601TB	600±25%	100	0.50	350
WLBD1608K1U102TB	1000±25%	100	0.70	200
WLBD1608H1U152TB	1500±25%	100	1.00	200
WLBD1608H1U202TB	2000±25%	100	1.20	150

Characteristic Curve

WLBD1608K1U300TB



WLBD1608K1U600TB



WLBD1608K1U121TB



WLBD1608K1U151TB



WLBD1608K1U221TB



WLBD1608K1U301TB



WLBD1608K1U471TB



WLBD1608K1U601TB



WLBD1608K1U102TB



WLBD1608H1U152TB



WLBD1608H1U202TB



WLBD1608K1U800TB



Test condition & Requirements

<table>
<tr><th>Item</th><th>Performance</th><th>Test Condition</th></tr>
<tr><td>Operating Temperature</td><td>-40~+125℃
(Including self-temperature rise)</td><td>--</td></tr>
<tr><td>Transportation
Storage Temperature</td><td>-40~+125℃
(on board)</td><td>For long storage conditions, please see the Application Notice</td></tr>
<tr><td>Impedance (Z)</td><td rowspan="5">Refer to standard electrical characteristics list</td><td>Agilent4291</td></tr>
<tr><td>Inductance (Ls)</td><td>Agilent E4991</td></tr>
<tr><td>Q Factor</td><td>Agilent4287</td></tr>
<tr><td>DC Resistance</td><td>Agilent16192
Agilent 4338</td></tr>
<tr><td>Rated Current</td><td>DC Power Supply
Over Rated Current requirements, there will be some risk</td></tr>
<tr><td>Temperature Rise Test</td><td>Rated Current < 1A ΔT 20℃Max
Rated Current ≧ 1A ΔT 40℃Max</td><td>1. Applied the allowed DC current.
2. Temperature measured by digital surface thermometer.</td></tr>
<tr><td>Resistance to Soldering Heat</td><td>Appearance：No damage.
Impedance：within±15% of initial value
Inductance：within±10% of initial value
Q：Shall not exceed the specification value.
RDC：within ±15% of initial value and shall not exceed the specification value</td><td>Number of heat cycles: 1
<table><tr><th>Temperature (℃)</th><th>Time (s)</th><th>Temperature ramp/immersion and emersion rate</th></tr><tr><td>260 ±5 (solder temp)</td><td>10 ±1</td><td>25mm/s ±6 mm/s</td></tr></table>Depth: completely cover the termination</td></tr>
<tr><td>Solderability</td><td>More than 95% of the terminal electrode should be covered with solder.
  </td><td>Preheat: 150℃,60sec.
Solder: Sn96.5%-Ag3%-Cu0.5%
Solder temperature: 245±5℃
Flux for lead free: Rosin. 9.5%
Depth: completely cover the termination.
Dip time: 4±1sec.</td></tr>
<tr><td>Terminal strength</td><td>Appearance：No damage.
Impedance：within±15% of initial value
Inductance：within±10% of initial value
Q：Shall not exceed the specification value.
RDC：within ±15% of initial value and shall not exceed the specification value
  </td><td>Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020D Classification Reflow Profiles)
Component mounted on a PCB apply a force (>0805:1kg <=0805:0.5kg)to the side of a device being tested. This force shall be applied for 60 +1 seconds. Also the force shall be applied gradually as not to shock the component being tested.</td></tr>
<tr><td>Bending</td><td>Appearance：No damage.
Impedance：within±10% of initial value
Inductance：within±10% of initial value
Q：Shall not exceed the specification value.
RDC：within ±15% of initial value and shall not exceed the specification value</td><td>Shall be mounted on a FR4 substrate of the following dimensions:>=0805:40x100x1.2mm
<0805:40x100x0.8mm
Bending depth:>=0805:1.2mm
<0805:0.8mm
Duration of 10 sec for a min.</td></tr>
<tr><td>Vibration Test</td><td>Appearance：No damage.
Impedance：within±15% of initial value
Inductance：within±10% of initial value
Q：Shall not exceed the specification value.
RDC：within ±15% of initial value and shall not exceed the specification value</td><td>Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020D Classification Reflow Profiles)
Oscillation Frequency: 10～2K～10Hz for 20 minutes
Equipment： Vibration checker
Total Amplitude:1.52mm±10%
Testing Time : 12 hours(20 minutes, 12 cycles each of 3 orientations)。</td></tr>
<tr><td>Shock</td><td>Appearance：No damage.
Impedance：within±10% of initial value
Inductance：within±10% of initial value
Q：Shall not exceed the specification value.
RDC：within ±15% of initial value and shall not exceed the specification value</td><td>Test condition:
<table><tr><th>Type</th><th>Peak Value (g's)</th><th>Normal duration (D) (ms)</th><th>Wave form</th><th>Velocity change (Vi)ft/sec</th></tr><tr><td>SMD</td><td>50</td><td>11</td><td>Half-sine</td><td>11.3</td></tr><tr><td>Lead</td><td>50</td><td>11</td><td>Half-sine</td><td>11.3</td></tr></table></td></tr>
</table>

Item	Performance	Test Condition
Life test	Appearance: no damage. Impedance: within±15%of initial value. Inductance: within±10%of initial value. Q：Shall not exceed the specification value. RDC：within ±15% of initial value and shall not exceed the specification value	Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020D Classification Reflow Profiles) Temperature: 125±2℃(bead), 105±2℃(Inductor)) Applied current: rated current. Duration: 1000±12hrs. Measured at room temperature after placing for 24±2 hrs.
Load Humidity		Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020D Classification Reflow Profiles) Humidity: 85±2%R.H. Temperature: 85±2℃. Duration: 1000hrs Min. with 100% rated current. Measured at room temperature after placing for 24±2 hrs.
Thermal shock	Appearance: no damage. Impedance: within±15%of initial value. Inductance: within±10%of initial value. Q：Shall not exceed the specification value. RDC：within ±15% of initial value and shall not exceed the specification value	Preconditioning: Run through IR reflow for 2 times.(IPC/JEDEC J-STD-020D Classification Reflow Profiles) Condition for 1 cycle Step1: -40±2℃ 30±5 min. Step2: 25±2℃ ≦0.5min Step3: +125±2℃ 30±5min. (Bead) Step3: +105±2℃ 30±5min. (Inductor) Number of cycles: 500 Measured at room temperature after placing for 24±2 hrs.
Insulation Resistance	IR>1GΩ	Chip Inductor Only Test Voltage:100±10%V for 30Sec.

****Derating Curve**

For the ferrite chip bead which withstanding current over 1.5A, as the operating temperature over 85℃, the derating current information is necessary to consider with. For the detail derating of current, please refer to the Derated Current vs. Operating Temperature curve.



Soldering and Mounting



	L (mm)	G (mm)	H (mm)
WLBD1608	**2.6**	**0.6**	**0.8**

Soldering

Mildly activated rosin fluxes are preferred. The terminations are suitable for re-flow soldering systems. If hand soldering cannot be avoided, the preferred technique is the utilization of hot air soldering tools.

Note. If wave soldering is used ,there will be some risk.
Re-flow soldering temperatures below 240 degrees, there will be non-wetting risk

Lead Free Solder re-flow

Recommended temperature profiles for lead free re-flow soldering in Figure 1. (Refered to J-STD-020C)

Soldering Iron:

Products attachment with a soldering iron is discouraged due to the inherent process control limitations. If a soldering iron must be employed the following precautions are recommended. for Iron Soldering in Figure 2.

- Preheat circuit and products to 150℃
- 350℃ tip temperature (max)
- Never contact the ceramic with the iron tip
- 1.0mm tip diameter (max)
- Use a 20 watt soldering iron with tip diameter of 1.0mm
- Limit soldering time to 4~5sec.



Reflow times: 3 times max
Fig.1



Iron Soldering times：1 times max
Fig.2

Packaging Specification

Reel Dimension



Type	A(mm)	B(mm)	C(mm)	D(mm)
7"x8mm	9.0±0.5	60±2	13.5±0.5	178±2
7"x12mm	13.5±0.5	60±2	13.5±0.5	178±2

Tape Dimension / 8mm

■Material of taping is paper



Size	Bo(mm)	Ao(mm)	Ko(mm)	P(mm)	t(mm)
WLBD1608	1.80±0.05	0.96+0.05/-0.03	0.95±0.05	4.0±0.10	0.95±0.05



The force for tearing off cover tape is 15 to 60 grams in the arrow direction under the following conditions

Room Temp. (℃)	Room Humidity (%)	Room atm (hPa)	Tearing Speed mm/min
5~35	45~85	860~1060	300

Products meet IPC/JEDEC J-STD-020D standard-MSL, level 1.

Quantity per reel ：4K pcs / reel