



NOTES:

1. SUPPLIED ON TAPE AND REEL ONLY.

TAPE AND REEL SPECIFICATIONS:

2. TAPE:

MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER

ANSI/EIA-481 STANDARD

.315 [8.0] WIDE; .157 [4.0] PITCH

3. REEL:

7.0 [177.8] DIA. 1000 PIECES OF
PART NO. 5015 PER REEL.

KEYSTONE ELECTRONICS CORP.

ASTORIA, N.Y. 11105-2017

PART NAME

TEST POINT, MINIATURE, SURFACE MOUNT

MATERIAL

.010 [0.25] TH'K PHOSPHOR BRONZE

FINISH

TIN LEAD PLATE

DRN BY

BOONE

DATE

2/7/07

APP'D

SCALE

10X, 1X

6.18.15 PER ECR 15-042 SPLIT C/M DWG

A

TOLERANCES

INCH [MM]

DECIMAL

± .005 [± 0.13]

ANGULAR

± 1°

UNLESS OTHERWISE SPECIFIED

CODE

C

DWG NO.

9-5015-TL

DATE

DESCRIPTION

REV.