# Kingbright

Part Number: KB356NT


#### **Features**


- 1. High collector-emitter Voltage.
- 2. Opaque type, mini-flat package.
- 3. Subminiature type (The volume is smaller than that of our conventional DIP type by as far as 30%).
- 4.Isolation voltage between input and output Viso:3750Vrms.
- 5. Employs double transfer mold technology.
- 6. Recognized by UL and CUL, file NO. E225308.
- 7.Approved by VDE 0884 Teil2(NO:40017614).
- 8.Package: 1000pcs / reel.
- 9. Moisture sensitivity level: 4.
- 10.RoHS Compliant.

#### **Applications**

- 1. Hybrid substrates that require high density mounting.
- 2. Programmable controllers.

# \*PACKAGE DIMENSIONS (UNIT:mm) SMD Type





UNIT: MM[INCH]

TOLERANCE:  $\pm 0.5[\pm 0.02]$  UNLESS OTHERWISE NOTED.





SPEC NO: DSAD2840 REV NO: V.25 DATE: MAR/20/2017 PAGE: 1 OF 8

APPROVED: Wynec CHECKED: Tracy Deng DRAWN: L.T.Zhang ERP: 1205000037





Part Number: KB356NT

# \*Absolute Maximum Ratings (Ta=25°C)

| Parameter                |                             | Symbol | Rating      | Unit |
|--------------------------|-----------------------------|--------|-------------|------|
| Input                    | Forward current             | lF     | 50          | mA   |
|                          | Reverse Voltage             | VR     | 6           | V    |
|                          | Power dissipation           | Po     | 70          | mW   |
| Output                   | Collector-emitter voltage   | VCEO   | 80          | V    |
|                          | Emitter-collector voltage   | Veco   | 6           | V    |
|                          | Collector current           | Ic     | 50          | mA   |
|                          | Collector power dissipation | Pc     | 150         | mW   |
| Total power dissipation  |                             | Ptot   | 170         | mW   |
| *1 Isolation voltage     |                             | V iso  | 3750        | Vrms |
| Operating temperature    |                             | T opr  | -30 to +100 | °C   |
| Storage temperature      |                             | T stg  | -40 to +125 | °C   |
| *2 Soldering temperature |                             | Tsol   | 260         | °C   |

<sup>\*1 40</sup> to 60% RH,AC for 1 minute.

# \*Electro-optical Characteristics

| Parameter       |                                      | Symbol    | Conditions        | Min.                                   | Тур. | Max. | Unit             |    |
|-----------------|--------------------------------------|-----------|-------------------|--|------|------|------------------|----|
| Input           | Forward voltage                      |           | VF                | IF=20mA                                | -    | 1.2  | 1.4              | V  |
|                 | Peak forward voltage                 |           | VFM               | IFM=0.5A                               | -    | -    | 3.0              | V  |
|                 | Reverse current                      |           | lr                | VR=4V                                  | -    | -    | 10               | uA |
| Output          | Collector dark current               |           | ICEO              | V ce = 20V IF =0                       | -    | -    | 10 <sup>-7</sup> | Α  |
|                 | Collector-emitter breakdown voltage  |           | BV <sub>CEO</sub> | I <sub>c</sub> =0.1mA IF=0             | 80   | -    | -                | V  |
|                 | Emitter-collector breakdown voltage  |           | BV <sub>ECO</sub> | I <sub>E</sub> =10uA IF=0              | 6    | -    | -                | V  |
| Transfer        | Current transfer ratio               |           | CTR               | IF=5mA Vce=5V                          | 50   | -    | 600              | %  |
|                 | Collector-emitter saturation voltage |           | VCE (sat)         | IF=20mA IC=1mA                         | -    | 0.1  | 0.2              | V  |
| characteristics | Response                             | Rise time | Τr                | V <sub>ce</sub> = 2V IC=2mA<br>RL=100Ω | -    | 6    | -                | uS |
|                 |                                      | Fall time | T f               |  | -    | 8    | -                | uS |

SPEC NO: DSAD2840 REV NO: V.25 DATE: MAR/20/2017 PAGE: 2 OF 8

APPROVED: Wynec CHECKED: Tracy Deng DRAWN: L.T.Zhang ERP: 1205000037

<sup>\*2</sup> For 10 seconds.

<sup>&</sup>lt;sup>\*3</sup> Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.



Part Number: KB356NT

| Model No. | Rank mark            | CTR(%)     |  |  |
|-----------|----------------------|------------|--|--|
| KB356NLT  | L                    | 50 to 100  |  |  |
| KB356N1T  | Α                    | 80 to 160  |  |  |
| KB356N2T  | В                    | 130 to 260 |  |  |
| KB356N3T  | С                    | 200 to 400 |  |  |
| KB356N4T  | D                    | 300 to 600 |  |  |
| KB356N5T  | A or B               | 80 to 260  |  |  |
| KB356N6T  | B or C               | 130 to 400 |  |  |
| KB356N7T  | C or D               | 200 to 600 |  |  |
| KB356N8T  | A,B or C             | 80 to 400  |  |  |
| KB356N9T  | B,C or D             | 130 to 600 |  |  |
| KB356N0T  | A,B,C or D           | 80 to 600  |  |  |
| KB356NT   | L,A,B,C,D or No mark | 50 to 600  |  |  |

SPEC NO: DSAD2840 REV NO: V.25 DATE: MAR/20/2017 PAGE: 3 OF 8

APPROVED: Wynec CHECKED: Tracy Deng DRAWN: L.T.Zhang ERP: 1205000037

# Kingbright

Part Number: KB356NT

Fig. 1 Current Transfer vs. Forward Current




Fig. 3 Collector Current vs.
Collector-emitter Voltage




Fig. 5 Collector-emitter Saturation Voltage vs. Ambient Temperature




Fig. 2 Forward Current vs. Forward voltage




Fig. 4 Relative Current Transfer Ratio vs.Ambient Temperature





Fig. 6 Response Time vs. Load Resistance



SPEC NO: DSAD2840 REV NO: V.25
APPROVED: Wynec CHECKED: Tracy Deng

DATE: MAR/20/2017 DRAWN: L.T.Zhang PAGE: 4 OF 8 ERP: 1205000037

# Kingbright

Part Number: KB356NT

Fig. 7 Collector-emitter Saturation Voltage vs. Forward Current






Fig. 8 Collector Dark Current vs.
Ambient Temperature



**Test Circuit for Response Time** 



SPEC NO: DSAD2840 REV NO: V.25 DATE: MAR/20/2017 PAGE: 5 OF 8

APPROVED: Wynec CHECKED: Tracy Deng DRAWN: L.T.Zhang ERP: 1205000037






Part Number: KB356NT

#### \*NOTES ON HANDLING

#### 1. Cautions regarding noise

Be aware that power is suddenly into the componment any surge current may cause damage happen, even if the voltage is within the absolute maximum ratings.



1. Don't cause stress to the LEDs while it is exposed to high temperature.

- 2. The maximum number of reflow soldering passes is 2 times.
- Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

#### **CAUTION**

Within this device there exists GaAs (Gallium Arsenide) material which is a harmful substance if ingested. GaAs dust and fumes are toxic. Do not break, cut or pulverize the product, or use chemicals to dissolve them.

#### **RESTRICTIONS ON PRODUCT USE**

- The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version. Not all devices / types available in every country.
- We are mention about our product quality stablity, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing KINGBRIGHT products, to observe standards of safety, and to a avoid situations in which a malfunction or failure of a KINGBRIGHT product could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that KINGBRIGHT products are used within specified operating ranges as set forth in the most recent products specifications.

SPEC NO: DSAD2840 REV NO: V.25 DATE: MAR/20/2017 PAGE: 6 OF 8

APPROVED: Wynec CHECKED: Tracy Deng DRAWN: L.T.Zhang ERP: 1205000037


# **Kingbright**

### **PHOTOCOUPLER**


Part Number: KB356NT

# **Outline and Dimension (Tape)**


(Units: mm) TAPE



### **Tape Direction**



### Outline and Dimension(Reel)



Packing:1000pcs/reel


SPEC NO: DSAD2840 APPROVED : Wynec REV NO: V.25 CHECKED: Tracy Deng DATE: MAR/20/2017 DRAWN: L.T.Zhang PAGE: 7 OF 8 ERP: 1205000037


# **Kingbright**

#### **PHOTOCOUPLER**

Part Number: KB356NT

#### **PACKING & LABEL SPECIFICATIONS**







SPEC NO: DSAD2840 APPROVED : Wynec REV NO: V.25 CHECKED: Tracy Deng DATE: MAR/20/2017 DRAWN: L.T.Zhang PAGE: 8 OF 8 ERP: 1205000037