





5 4 3 2 1

Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802




PCB layout hole
component side
(PCB holes plating : Tin)



Connector retention and insertion forces on the PCB = 25 / 80 newtons

09 66 252 6611	M 3	2			
09 66 252 7611	M 3	3			
09 66 252 5611	M 3	0.76 µm Au			
09 66 252 6612	4-40 UNC	2			
09 66 252 7612	4-40 UNC	3			
09 66 252 5612	4-40 UNC	0.76 µm Au	27960	05/dec/00	ALSPACE
Part number	Nut thread	Performance level	Mod.	Dat.	Name

	Dat.	Name
Detail.	05/dec/00	ALSPACE
Insp.		
Stand.		



All Dim. in mm
Orig. Size DIN A 4

D-Sub 15 poles standard angle
female, solder pin with nut and
grounding board lock.

Maßstab/
Scale

1.5:1

HARTING EURL
F-95972 Paris



TB 0966252x61x

Blatt/ Page

5 / 6

Sub.

09 66 252 5612
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 252 5611
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



Data sheets are available in following formats
2D files

Typenblatt

Typenblatt

09 66 252 6611
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 252 6612
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 252 7611
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 252 7612
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell
Number of contacts	15 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF