




09 65 422 6801	M3	2					Dat.	Name		D-Sub, male, standard angle, 37 poles, with solder pin, nut and hole	Maßstab/ Scale 1.5:1	
09 65 422 7801	M3	3				Detail.	12/dec/00	ALSPACE				
09 65 422 5801	M3	0.76 µm Au				Insp.						All Dim. in mm Orig. Size DIN A 4
09 65 422 6802	4-40 UNC	2	29773	18-APR-02	CV	Stand.						
09 65 422 7802	4-40 UNC	3	29689	02/07/01	AA	HARTING EURL F-95972 Paris				TB 0965422x80x	Blatt/ Page 2/	
09 65 422 5802	4-40 UNC	0.76 µm Au	27960	12/dec/00	ALSPACE							
Part number	Nut thread	Performance level	Mod.	Dat.	Name				Sub.			

09 65 422 5803
Printed board connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	37 way
Row pitch	Row separation 2.54 mm
Board fixing	without grounding board lock
flange	with screw lock UNC 4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

The data sheet is up to date
2D files

Typenblatt

Typenblatt

09 65 422 5801

Printed board connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	37 way
Row pitch	Row separation 2.54 mm
Board fixing	without grounding board lock
flange	M 3
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



The data sheet is up to date
2D files

Typenblatt

Typenblatt

09 65 422 5802
Printed board connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	37 way
Row pitch	Row separation 2.54 mm
Board fixing	without grounding board lock
flange	UNC4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



The data sheet is up to date
2D files

Typenblatt

Typenblatt

09 65 422 5800
Printed board connector

Other applications

gender	male connector, right angled
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	37 way
Row pitch	Row separation 2.54 mm
Board fixing	without grounding board lock
flange	hole 3.1 mm
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



The data sheet is up to date
2D files

Typenblatt

Typenblatt