

International TOR Rectifier

IRFR/U3303

HEXFET® Power MOSFET

- Ultra Low On-Resistance
- Surface Mount (IRFR3303)
- Straight Lead (IRFU3033)
- Advanced Process Technology
- Fast Switching
- Fully Avalanche Rated






Description

Fifth Generation HEXFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that HEXFET Power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The D-Pak is designed for surface mounting using vapor phase, infrared, or wave soldering techniques. The straight lead version (IRFU series) is for through-hole mounting applications. Power dissipation levels up to 1.5 watts are possible in typical surface mount applications.



Absolute Maximum Ratings

	Parameter	Max.	Units	
I _D @ T _C = 25°C	Continuous Drain Current, V _{GS} @ 10V	33⑤		
I _D @ T _C = 100°C	Continuous Drain Current, V _{GS} @ 10V	21⑤	Α	
I _{DM}	Pulsed Drain Current ①	120		
P _D @T _C = 25°C	Power Dissipation	57	W	
	Linear Derating Factor	0.45	W/°C	
V_{GS}	Gate-to-Source Voltage	± 20	V	
E _{AS}	Single Pulse Avalanche Energy®	95	mJ	
I _{AR}	Avalanche Current①	18	Α	
E _{AR}	Repetitive Avalanche Energy ①	5.7	mJ	
dv/dt	Peak Diode Recovery dv/dt ③	5.0	V/ns	
TJ	Operating Junction and	-55 to + 150		
T _{STG}	Storage Temperature Range		°C	
	Soldering Temperature, for 10 seconds	300 (1.6mm from case)		

Thermal Resistance

	Parameter	Тур.	Max.	Units
R _θ JC	Junction-to-Case		2.2	
$R_{\theta JA}$	Junction-to-Ambient (PCB mount)**		50	°C/W
$R_{\theta JA}$	Junction-to-Ambient		110	

IRFR/U3303

Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

	Parameter	Min.	Тур.	Max.	Units	Conditions
V _{(BR)DSS}	Drain-to-Source Breakdown Voltage	30			V	$V_{GS} = 0V, I_D = 250\mu A$
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient		0.032		V/°C	Reference to 25°C, I _D = 1mA
R _{DS(on)}	Static Drain-to-Source On-Resistance			0.031	Ω	V _{GS} = 10V, I _D = 18A ④
V _{GS(th)}	Gate Threshold Voltage	2.0		4.0	V	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$
g _{fs}	Forward Transconductance	9.3			S	V _{DS} = 25V, I _D = 18A
	Drain-to-Source Leakage Current			25		$V_{DS} = 30V, V_{GS} = 0V$
I _{DSS}	Dialific-Source Leakage Current			250	μA	V _{DS} = 24V, V _{GS} = 0V, T _J = 150°C
	Gate-to-Source Forward Leakage			100	- A	V _{GS} = 20V
I _{GSS}	Gate-to-Source Reverse Leakage			-100	nA	V _{GS} = -20V
Qg	Total Gate Charge			29		I _D = 18A
Q _{gs}	Gate-to-Source Charge			7.3	nC	$V_{DS} = 24V$
Q _{gd}	Gate-to-Drain ("Miller") Charge			13		V _{GS} = 10V, See Fig. 6 and 13 ④
t _{d(on)}	Turn-On Delay Time		11			$V_{DD} = 15V$
t _r	Rise Time		99		_	I _D = 18A
t _{d(off)}	Turn-Off Delay Time		16		ns	$R_G = 13\Omega$
t _f	Fall Time		28			$R_D = 0.8\Omega$, See Fig. 10 \oplus
1	Internal Prain Industance		4.5			Between lead,
L _D	Internal Drain Inductance		4.5			6mm (0.25in.)
L _S	Internal Source Inductance		7.5		nH 	from package
						and center of die contact®
Ciss	Input Capacitance		750			V _{GS} = 0V
C _{oss}	Output Capacitance		400		pF	$V_{DS} = 25V$
C _{rss}	Reverse Transfer Capacitance		140			f = 1.0MHz, See Fig. 5

Source-Drain Ratings and Characteristics

	Parameter	Min.	Тур.	Max.	Units	Conditions	
Is	Continuous Source Current			00@		MOSFET symbol	
	(Body Diode)		33®	339	Α	showing the	
I _{SM}	Pulsed Source Current				120		integral reverse
	(Body Diode) ①			120		p-n junction diode.	
V _{SD}	Diode Forward Voltage			1.3	V	T _J = 25°C, I _S = 18A, V _{GS} = 0V ④	
t _{rr}	Reverse Recovery Time		53	80	ns	T _J = 25°C, I _F = 18A	
Q _{rr}	Reverse RecoveryCharge		94	140	nC	di/dt = 100A/µs ④	
t _{on}	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by L _S +L _D)					

Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature. (See fig. 11)
- Starting $T_J = 25$ °C, $L = 590 \mu H$ $R_G = 25 Ω$, $I_{AS} = 18 A$. (See Figure 12)
- $\label{eq:loss} \begin{array}{l} \text{ $I_{SD} \leq 18$A, di/dt} \leq 140$A/\mu s, $V_{DD} \leq V_{(BR)DSS}$,} \\ T_{J} \leq 150^{\circ}\text{C} \end{array}$
- ⓐ Pulse width ≤ 300 μ s; duty cycle ≤ 2%.
- ⑤ Caculated continuous current based on maximum allowable junction temperature; Package limitation current = 20A.
- 6 This is applied for I-PAK, L_S of D-PAK is measured between lead and center of die contact
- ** When mounted on 1" square PCB (FR-4 or G-10 Material).
 For recommended footprint and soldering techniques refer to application note #AN-994





Fig 1. Typical Output Characteristics

Fig 2. Typical Output Characteristics






Fig 3. Typical Transfer Characteristics

Fig 4. Normalized On-Resistance Vs. Temperature





Fig 5. Typical Capacitance Vs. Drain-to-Source Voltage

Fig 6. Typical Gate Charge Vs. Gate-to-Source Voltage

OPERATION IN THIS AREA LIMI BY R_{DS(on)}

1000






Fig 7. Typical Source-Drain Diode Forward Voltage

Fig 8. Maximum Safe Operating Area




Fig 9. Maximum Drain Current Vs. Case Temperature




Fig 10a. Switching Time Test Circuit




Fig 10b. Switching Time Waveforms




Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Case




Fig 12a. Unclamped Inductive Test Circuit




Fig 12b. Unclamped Inductive Waveforms




Fig 13a. Basic Gate Charge Waveform




Fig 12c. Maximum Avalanche Energy Vs. Drain Current






Fig 13b. Gate Charge Test Circuit

Peak Diode Recovery dv/dt Test Circuit






 * V_{GS} = 5V for Logic Level Devices

Fig 14. For N-Channel HEXFETS

Package Outline


TO-252AA Outline

Dimensions are shown in millimeters (inches)



Part Marking Information


TO-252AA (D-Pak)




Package Outline

TO-251AA Outline

Dimensions are shown in millimeters (inches)




Part Marking Information TO-251AA (I-Pak)



Tape & Reel Information

TO-252AA



International

WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, Tel: (310) 322 3331 EUROPEAN HEADQUARTERS: Hurst Green, Oxted, Surrey RH8 9BB, UK Tel: ++ 44 1883 732020 IR CANADA: 7321 Victoria Park Ave., Suite 201, Markham, Ontario L3R 2Z8, Tel: (905) 475 1897 IR GERMANY: Saalburgstrasse 157, 61350 Bad Homburg Tel: ++ 49 6172 96590

IR ITALY: Via Liguria 49, 10071 Borgaro, Torino Tel: ++ 39 11 451 0111

IR FAR EAST: K&H Bldg., 2F, 30-4 Nishi-Ikebukuro 3-Chome, Toshima-Ku, Tokyo Japan 171 Tel: 81 3 3983 0086
IR SOUTHEAST ASIA: 315 Outram Road, #10-02 Tan Boon Liat Building, Singapore 0316 Tel: 65 221 8371

http://www.irf.com/ Data and specifications subject to change without notice. 8/97

Note: For the most current drawings please refer to the IR website at: http://www.irf.com/package/