



Part No.	Emitting Color + Material	λ_D (nm)	Lens Type	Iv (mcd) @10mA *20mA		Viewing Angle	Dimension
				Min.	Typ.		

L704HD	GaP	660	red diffused	0.5	1	110°	3mm x 3mm Square
L704ID	GaAsP/GaP	625	red diffused	3	5	110°	
L704ED	GaAsP/GaP	625	orange diffused	3	5	110°	
L704GD	GaP	568	green diffused	1	5	110°	
L704YD	GaAsP/GaP	588	yellow diffused	1	5	110°	
L704SRD	GaAlAs	640	red diffused	*40	*70	110°	

L714HD	GaP	660	red diffused	0.5	1	110°	3mm x 3mm Square
L714ID	GaAsP/GaP	625	red diffused	3	5	110°	
L714ED	GaAsP/GaP	625	orange diffused	3	5	110°	
L714GD	GaP	568	green diffused	1	5	110°	
L714YD	GaAsP/GaP	588	yellow diffused	1	5	110°	
L714SRD	GaAlAs	640	red diffused	*40	*70	110°	

L1553HDT	GaP	660	red diffused	0.5	1	110°	5mm x 5mm Square
L1553IDT	GaAsP/GaP	625	red diffused	3	8	110°	
L1553EDT	GaAsP/GaP	625	orange diffused	3	8	110°	
L1553GDT	GaP	568	green diffused	1	5	110°	
L1553YDT	GaAsP/GaP	588	yellow diffused	1	5	110°	
L1553SRDT	GaAlAs	640	red diffused	*36	*80	110°	

L503HDT	GaP	660	red diffused	0.5	1	110°	5mm x 5mm Square
L503IDT	GaAsP/GaP	625	red diffused	3	6	110°	
L503GDT	GaP	568	green diffused	1	3	110°	
L503YDT	GaAsP/GaP	588	yellow diffused	1	3	110°	

NOTES :

1. All dimensions are in millimeters (inches)
2. Tolerance is $\pm 0.25\text{mm}$ (0.01") unless otherwise noted.