

## SUMMARY

### # Wires

Low	0
High	0
Coax	1
Triax	0
Quad	0
Fiber	0
Fluidic	0
Material	Brass



Series	00
Termination type	Female print PCB
IP rating	50
Cable Ø (mm)	0.00 - 0.00
Wire size / AWG	0.00 - 0.00

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model	XSG*: Elbow receptacle, two nuts, threaded shell, for printed circuit, coaxial.
Keying	Circular (can rotate)
Housing Material	Brass (nickel plated) shell, collet nut, latch sleeve and mid pieces
Cable Fixing	: 0 - 0 mm
Variant	

### Performance

Configuration	0.25 : 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated Current	4


### Specifications

Contact Type:	Coaxial 50 Ohm (Printed Circuit Board)
Max. Matings:	5000
Contact Dia.:	0.7 mm (0.028in)
R (max):	6.1 mOhm

### Others

Endurance (Shell):	5000 mating cycles
F ret (min):	100 N
IP Rating:	50

## Draws



	A	L	e
mm.	10	17.5	M7x0.5
in.	0.39	0.69	

## Tools

Spanner: DCB.91.455.0LN

## Cables