




Fig. 1

- Series 380 & 480 use M-M #8000 pins. See page 174 for details.
- Series 329 & 429 use M-M #2954 pin receptacles and accept pin diameters from 0,38 - 0,64. See page 140 for details.
- Series 329 & 429 receptacles use Hi-Rel, 4 finger #30 contacts rated at 3 amps. See page 208 for details.
- Solder cups are pre-aligned.





Fig. 2

Ordering Information

Fig. 1

Series 380...001

Solder Cup / Solder Tail

380-XX-1 _ _ -00-001000

Specify # of pins

01-64

Fig. 2

Series 480...001

Solder Cup / Solder Tail

480-XX-2 _ _ -00-001000

Specify # of pins

02-64




Fig. 3



XX= Plating Code
See Below

For RoHS compliance, select plating code.
For the gold option (XX=10) also change
part number from X80-XX-XXX-00-001000
to X80-10-XXX-00-001100

SPECIFY PLATING CODE XX=

10

90

40

Pin Plating



0,25µm Au

5,08µmSn/Pb

5,08µmSn

Fig. 3

Series 329...540

Solder Cup Sockets

329-XX-1 _ _ -41-540000

Specify # of pins

01-64

Fig. 4

Series 429...540

Solder Cup Sockets

429-XX-2 _ _ -41-540000

Specify # of pins

02-64



XX= Plating Code
See Below

For RoHS compliance, select plating code.
For the gold option (XX=13) also change
part number from X29-XX-XXX-41-540000
to X29-13-XXX-41-540100

SPECIFY PLATING CODE XX=

13

93

43

Sleeve (Pin)




0,25µmAu

5,08µmSn/Pb

5,08µmSn

Contact (Clip)



0,76µmAu

0,76µmAu

0,76µmAu

Fig. 4