


FEATURES

- * High speed transmission (16 Mbps , NRZ code)
- * TTL compatible
- * Same package as fiber optic transmitting module LTDL-TX12P05

APPLICATIONS

- * Digital audio system
- * CD & DVD players

PACKAGE DIMENSIONS



NOTES:

1. All dimensions are in millimeters.
2. Tolerance is ± 0.3 mm unless otherwise noted.



LITE-ON TECHNOLOGY CORPORATION

Property of Lite-On Only

ELECTRO - OPTICAL CHARACTERISTICS


ABSOLUTE MAXIMUM RATINGS AT Ta=25

PARAMETER	MAXIMUM RATING	UNIT
Supply Voltage (V _{DD})	6.0	V
Output Voltage (V _O)	V _{DD} + 0.3	V
Operating Temperature Range	-20 to + 70	
Storage Temperature Range	-30 to + 80	
Lead Soldering Temperature [1.6mm(.063") From Body]	260 for 5 Seconds	


ELECTRICAL OPTICAL CHARACTERISTICS AT Ta=25

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Data Rate	T _s	0.1	-	16	Mbps	NRZ signal
Operating Voltage	V _{DD}	4.75	-	5.25	V	
Peak Sensitivity Wavelength	λ_{Peak}	-	650	-	nm	
Input Sensitivity	P _i	-24	-	-14	dBm	
Dissipation current	I _{DD}	2	7	10	mA	NRZ signal
High level output voltage	V _{OH}	2.4	4.8	-	V	Dc Light , I _{OH} = -20 μ A
Low level output voltage	V _{OL}	-	0.2	0.4	V	Dark , I _{OL} = 0.6mA
“Low $\rightarrow$ High” propagation delay time	t _{PLH}	-	-	166	ns	*1
“High $\rightarrow$ Low” propagation delay time	t _{PHL}	-	-	166	ns	
Pulse width distortion	Δt_w	-18	-	+18	ns	
Jitter	Δt_j	-	1	5	ns	*1
Rise Time	t _r	-	8	20	ns	*1
Fall Time	t _f	-	8	20	ns	*1

*1 Setup of Measuring System



Rise and Fall Times and Pulse Width Distortion



$$\text{Pulse Width Distortion} = \Delta t_w = t_{PHL} - t_{PLH}$$

Jitter

