

1305 1305-0-15-XX-47-XX-04-0 Press-fit in .061 mounting hole	1306 1306-0-15-XX-47-XX-04-0 Press-fit in .061 mounting hole.	7305 7305-0-15-XX-47-XX-10-0 Solder mount in .060 min. hole.	0400 0400-0-15-XX-47-XX-04-0 Press-fit in .067 mounting hole.
0335 0335-0-15-XX-47-XX-04-0 Hex press-fit in .064 plated thru hole	4614 4614-0-31-XX-47-XX-04-0 Compliant press-fit in .040±.003 plated hole. For .060→.100 thick board.	4615 4615-0-31-XX-47-XX-04-0 Compliant press-fit in .040±.003 plated hole. For .090→.130 thick board.	7614 7614-0-31-XX-47-XX-04-0 Compliant press-fit in .040±.003 plated hole. For .060→.100 thick board.
8401 8401-0-15-XX-47-XX-04-0 Hex press-fit in .063 plated thru hole	2400 2400-0-15-XX-47-XX-04-0 Press-fit in .066 mounting hole.	6857 6857-0-15-XX-47-XX-10-0 Press-fit in .061 mounting hole.	9393 9393-0-15-XX-47-XX-10-0 Press-fit in .067 mounting hole.

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - 47 - XX - XX - 0

BASIC PART # →

SPECIFY SHELL FINISH: →

01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH: →

01 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

CONTACT

#47 CONTACT (DATA ON PAGE 211)