

INDUCTOR FOR HARRIS SEMICONDUCTOR

Portable Power Converter HIP 5020 Eval 1



- ⊕ Surface mount, self-leaded inductor
- ⊕ Solution based on efficiency, using Allied Microlite core
- ⊕ Designed for Notebooks, portables and PCAs
- ⊕ Wide variety of other inductor sizes and values available


Electrical Specifications @ 25°C — Operating Temperature -30°C to +130°C

Pulse Part Number	Reference Values				Control Values		Calculation Data	
	I _{DC} (amp)	L @ DC L _{DC} (μH)	ET (V-μsec)	Storage Capacity (μJoules)	L w/o DC L _{0±20%} (μH)	DCR MAX (mΩ)	100 Gauss ET ₁₀₀ (V-μsec)	1 Amp DC H ₁ (Orsted)
P0119	4.96	7.4	14.34	90.43	12.7	18.2	1.20	7.42


NOTES:

1. The reference inductance is a typical value at the AC and DC excitation listed.
2. Temperature rise is 55° C in typical buck or boost circuits at 200 KHz and with the reference ET applied to the inductor.
3. Total loss in the inductor is 423 mWatts for 55°C temperature rise above ambient.
4. To estimate temperature rise in a given application, determine the total losses (copper losses + core losses), divide by 423 and multiply by 55.
5. To determine copper losses, calculate:
CopperLoss (mW) = I_{DC}² x R_N (with R_N in mΩ).
6. The maximum DCR listed is approximately 17% over the nominal DCR (R_N).
7. For core loss in mWatts, using frequency (f, Hz) and operating flux density (B, Gauss), calculate: 0.342 x 10⁻¹² x B^{2.13} x f^{1.52}.
8. For flux density (B, Gauss), calculate ET (V-μsec) for the application, divide by ET₁₀₀ factor from the table and multiply by 100.
9. For estimating L with DC current, calculate H by multiplying H₁ from the table by I_{DC} of the application. Using H determine the DC perm Factor (F_{UDC}). Multiply L w/o DC by F_{UDC} for L @ DC.
10. Add suffix "T" to part number for tape and reel package (i.e. P0119T).

Mechanical




Schematic



Weight 2.4 grams
Tube 30/tube

Suggested PCB Layout



A	B	C	D	E	F
.565	.570	.360	.450	.520	.460
14,35	14,48	9,14	11,43	13,21	11,68

Dimensions: $\frac{\text{Inches}}{\text{mm}}$
Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$