






STRAIGHT PLUG CRIMP TYPE

PAGE 1/2 ISSUE 03-03-17B SERIES BNC 75 HDTV PART NUMBER R142077747







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
Body	BRASS	BBR	
Center contact	BRASS	NPGR	
Outer contact	BRASS	NPGR	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Others parts	BRASS	BBR	
-	-	-	
-	-	-	



# **Technical Data Sheet**

STRAIGHT PLUG CRIMP TYPE

PAGE 2/2 ISSUE 03-03-17B SERIES BNC 75 HDTV PART NUMBER R142077747

#### **PACKAGING**

100	Contact us	Contact us
Standard	Unit	Other

#### **ELECTRICAL CHARACTERISTICS**

Impedance 75 Frequency DC-12 GHz **VSWR** 1.05 x F(GHz) Maxi 0.0350 Insertion loss 0.1 √F(GHz) dB Maxi RF leakage AD - F(GHz)) dB Maxi - ( Voltage rating 500 Veff Maxi Dielectric withstanding voltage 1500 Veff mini Insulation resistance 5000  $M\Omega$  mini

### **MECHANICAL CHARACTERISTICS**

Center contact retention

Axial force – Mating End
Axial force – Opposite end
Torque

10
N mini
N mini
N mini
N mini
N mini

Recommended torque

 Mating
 NA
 N.cm

 Panel nut
 NA
 N.cm

 Clamp nut
 NA
 N.cm

 A/F clamp nut
 0.0000
 mm

Mating life 1000 Cycles mini

Weight **11.9220** g

#### **ENVIRONMENTAL**

Operating temperature -65/+165 °C
Hermetic seal NA Atm.cm3/s
Panel leakage NA

#### **SPECIFICATION**

## **CABLE ASSEMBLY**

Stripping	а	b	С	d	е	f
mm	4	10.8	18	0	14	0

Assembly instruction: Crimp 02

Recommended cable(s)

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

#### Cable retention

- pull off 220 N mini - torque NA N.cm

## **TOOLING**

Part Number	Description	Hexagon
R282231000	CRIMPING TOOL	10.54
R282223000	CRIMPING TOOL	1.73

## **OTHER CHARACTERISTICS**

Data speed rate up to 12.5Gb/s