



25.4 SQUARE FLANGE, STRAIGHT JACKS, CRIMP TYPE, FOR FLEXIBLE CABLES




cable group	part number	Dimensions				captured center contact	assembly instructions	panel cut out	packaging
		A	B	C	D				
5/50/S	R164 282 000	1.05	3.11	5.41	44.1	no	M01	P05	50 pieces (*)
5/50/D	R164 283 000	1.05	3.11	5.8	44.1	no	M01		
10/50/S	R164 286 000	2.45	7.46	11.05	46.1	no	M01		
11/50/D	R164 286 200	2.45	7.46	11.4	46.1	no	M01		

BULKHEAD STRAIGHT JACKS, FULL CRIMP TYPE, FOR FLEXIBLE CABLES (panel sealed)



cable group	part number	dimensions				captured center contact	assembly instructions	panel cut out	note	packaging
		A	B	C	D					
5/50/S	R164 329 000	1.05	3.11	5.41	44.1	no	M01	P03	rear mount	50 pieces (*)
5/50/D	R164 329 200	1.05	3.11	5.8	44.1	no	M01	P03		
10/50/S	R164 331 000	2.45	7.46	11.05	46.1	no	M01	P03		
11/50/D	R164 331 200	2.45	7.46	11.4	46.1	no	M01	P03		

BULKHEAD STRAIGHT JACK, SOLDER TYPE, FOR SEMI RIGID CABLE (panel sealed)



cable group	part number	captured center contact	assembly instructions	panel cut out	note	packaging
.141"	R164 635 002	yes	M03	P03	Rear mount	50 pieces (*)

(*) For unit packaging, add "W" after the P/N.