

LUMOTAST 25, keylock switch, 1 removal position, 1 NO, Gold, Male quick connector / plug-in socket, 90°, latching, key removal position 0

DISCONTINUED



fields of application

- Measurement-control-regulation
- Mechanical and system engineering
- Signalling systems

special features

- Mounting hole diameter 16.2 mm
- Switching position: 1 x 90° latching
- Mounting depth behind the front panel only 30.7 mm with female quick connector
- Gold contacts for safe switching
- Reverse-polarity-secured terminal with 4-pole male quick connector and crimped ribbon cable
- Alternative: terminal with plug-in socket in PCB
- Water jet protection class IP 65 on front
- 1 NO gold contact (max. 35 V/100 mA)



description

lock manufacturer Kaba

technical data

➤ general

illuminated	No
Bezel color	black
Collar shape	square
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
Packaging	Box
Packaging unit	2 pcs.
Operating life	50,000 Cycles
Degree of protection, front side, according to DIN EN 60529	IP65
RoHS compliant	Yes
REACH compliant	Yes

➤ mounting diameters

direct links

- [RAFI eCatalog](#)

Mounting hole	16.2 mm
Mounting depth	30.7 mm
Installation height	32.3 mm
Outside dimension, length	25 mm
Outside dimension, width	25 mm

> mechanical data


Actuation function	latching
Operating torque	1.5 Nm
Contact function	1 NO
Contact system	Snap-action contact
Contact material	Gold
Locking position	10000
Number of locking positions	10,000
Key removal position	0
Rotating angle	90°
Fixing	Threaded ring
Terminal on the rear	Male quick connector / plug-in socket

> electrical data


Rated voltage, min.	0.02 V
Rated voltage, max.	35 V
Rated current, min.	0.0001 A
Rated current, max.	0.1 A

drawings


Dimensioned drawing



System drawing



System drawing



Mounting hole drawing

