


samtec

**MOLD-TO-POSITION
PRODUCT**

 Minimums or set-up charges
may apply. Call Samtec.

ICH-516-SGT



DIP SOCKET CARRIERS ICH SERIES

Mates with:
AP, APS, APO, APH,
APA, APE

Hi-Temp DIP's Allow For Customized Row Spacing

Samtec ICH Series DIP sockets for unusual centerline applications feature lead sockets designed to float and self-center during soldering. This body will withstand most vapor phase and infrared soldering temperatures.

Specifications:

**ICH
HI-TEMP**


Same as ICO except:
Insulation Material:
Black High Temperature
Thermoplastic
Temperature Range:
-55°C to +140°C
Heat Deflection Temp:
215°C @ 264 psi

TYPE CARRIER	ROW SPACE	NO. OF PINS	LEAD STYLE	PLATING OPTION	OPTION (Leave Blank for Standard Version)
ICH = Hi-Temp Polyester	-2 thru -19 = Row Spacing Row Spacing EXAMPLE: -3 = .300 centers	02 thru 40 = Total Number of Pins		GG = 30μ" Gold Contact 10μ" Gold Shell	-L = Locking Socket Requires Style -S, ZS or -P and .035"±.003" board hole.
	GT = 30μ" Gold Contact Tin Shell				
	TT = Tin Contact and Shell (Styles -S, -ZS, -C, -A, -L, -M, -N only)				
	ST = 10μ" Gold Contact Tin Shell (Styles -S & -ZS only)				

Low Insertion Force (LIF)
Contact Available.

-S or -A = Printed Circuit For LIF Specify -ZS or -ZA <table border="1"> <thead> <tr> <th>LEAD STYLE</th> <th>Y TAIL</th> <th>Z</th> </tr> </thead> <tbody> <tr> <td>-S or -ZS</td> <td>(3.18) .125</td> <td>(7.62) .300</td> </tr> <tr> <td>-A or -ZA</td> <td>(4.57) .180</td> <td>(8.89) .350</td> </tr> </tbody> </table> Locking lead (-L) available See OPTION.	LEAD STYLE	Y TAIL	Z	-S or -ZS	(3.18) .125	(7.62) .300	-A or -ZA	(4.57) .180	(8.89) .350	-B = Body Only For LIF Specify -ZB 	-P = Short Tail <table border="1"> <thead> <tr> <th>LEAD STYLE</th> <th>Z</th> </tr> </thead> <tbody> <tr> <td>-P</td> <td>(5.20) .205</td> </tr> </tbody> </table> Locking lead (-L) available See OPTION.	LEAD STYLE	Z	-P	(5.20) .205
LEAD STYLE	Y TAIL	Z													
-S or -ZS	(3.18) .125	(7.62) .300													
-A or -ZA	(4.57) .180	(8.89) .350													
LEAD STYLE	Z														
-P	(5.20) .205														
-L = Low Profile For LIF Specify -ZL 	-M = Low Profile For LIF Specify -ZM 	-N = Micro Socket For LIF Specify -ZN 	-C = Micro Socket For LIF Specify -ZC 												

Note:
This Series is non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047
 SAMTEC GERMANY • Tel: +49 (0) 89/89460-0 • Fax: +49 (0) 89/89460-299
 SAMTEC SCANDINAVIA • Tel: +46-84477280 • Fax: +46-87420413
 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502
 SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842
 SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340
 SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681
 SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520
 SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61
 SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690
 SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-53854047
 SAMTEC SOUTH AFRICA • Tel: 27 11 45281112 • Fax: 27 86 6714432
 SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113
 SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315
 SAMTEC INDIA • Tel: 91 80 306 21 612 • Fax: 91 80 4152 8187
 SAMTEC TAIWAN • Tel: 886 02 2698-3367 • Fax: 886 02 8698-2159
 SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745