





SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED VOLTAGE (SQUARE WAVE)	12	V _{p-p}
OPERATING VOLTAGE RANGE	3 ~ 18	V _{p-p}
RATED CURRENT (MAX)	8	mA
CAPACITANCE	11,000±30%	pF
MINIMUM SPL @ 10 CM	90	dBA
RESONANT FREQUENCY	3,600±500	Hz
OPERATING TEMPERATURE	-20 ~ +60	°C
STORAGE TEMPERATURE	-30 ~ +70	°C
HOUSING MATERIAL	ABS	—
TERMINAL MATERIAL	TIN-PLATED PBW	—
WEIGHT	3.8	grams

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	4/16/02	
A	REVISED TO NEW TEMPLATE	6/15/04	R. W.
B	ADDED NOTE 3	4/29/05	R. W.



1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. PART WASHABLE USING DEIONIZED WATER OR ISOPROPYL ALCOHOL.

TRANSDUCER(ELECTRO-MECH)
AT-24

APPROVALS	DATE
DRAWN <i>RABL</i>	4/02
APPROVED <i>S.J.</i>	4/02
DO NOT SCALE DRAWING	

SIZE
A

DRAWING NO.
AT-24

SCALE: N.T.S.

SHEET 1 OF 1

FILE NAME
AT-24.DWG