

# Surface Mount Automotive Transient Voltage Suppressors

High Temperature Stability and High Reliability Conditions

Patented\*

\* Patent #'s:  
4,980,315  
5,166,769  
5,278,095



DO-218AB

## FEATURES

- Patented PAR<sup>®</sup> construction
- Low leakage current
- Low forward voltage drop
- High surge capability
- Meets ISO7637-2 surge spec
- Meets MSL level 1, per J-STD-020C, LF max peak of 245 °C
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



## TYPICAL APPLICATIONS

Used in sensitive electronics protection against voltage transients induced by inductive load switching and lighting, especially for automotive load dump protection application.

## MECHANICAL DATA

**Case:** DO-218AB

Epoxy meets UL 94V-0 flammability rating

**Terminals:** Matte tin plated leads, solderable per J-STD-002B and JESD22-B102D

HE3 suffix for high reliability grade (AEC Q101 qualified)

**Polarity:** Heatsink is anode

## PRIMARY CHARACTERISTICS

$V_{BR}$	27 V
$P_{PPM}$ (10 x 1000 $\mu$ s)	6600 W
$P_D$	8.0 W
$I_{RSM}$	130 A
$I_{FSM}$	700 A
$T_J$ max.	175 °C

## MAXIMUM RATINGS ( $T_C = 25$ °C unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with 10/1000 $\mu$ s waveform	$P_{PPM}$	6600	W
Power dissipation on infinite heatsink at $T_C = 25$ °C (Fig. 1)	$P_D$	8.0	
Non-repetitive peak reverse surge current for 10 $\mu$ s/10 ms exponentially decaying waveform	$I_{RSM}$	130	A
Maximum working stand-off voltage	$V_{WM}$	22.0	V
Peak forward surge current 8.3 ms single half sine-wave	$I_{FSM}$	700	A
Operating junction and storage temperature range	$T_J, T_{STG}$	- 55 to + 175	°C

## ELECTRICAL CHARACTERISTICS ( $T_C = 25$ °C unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Reverse zener voltage	at 10 mA	$V_Z$	24.0		30.0	V
Zener voltage temperature coefficient	at $I_Z = 10$ mA	$V_{ZTC}$			36	mV/°C
Clamping voltage for 10 $\mu$ s/10 ms exponentially decaying waveform	at $I_{PP} = 75$ A	$V_C$			40.0	V
Instantaneous forward voltage <sup>(1)</sup>	at 6.0 A at 100 A	$V_F$		0.93	0.98	V
Reverse leakage current	at rated $V_{WM}$ $T_J = 25$ °C $T_J = 175$ °C	$I_R$			1.0 50.0	$\mu$ A

### Note:

(1) Measured on a 300  $\mu$ s square pulse width

**THERMAL CHARACTERISTICS** ( $T_C = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Typical thermal resistance, junction to case	$R_{\theta JC}$	0.90	$^{\circ}\text{C/W}$

**ORDERING INFORMATION** (Example)

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
SM8A27HE3/2D	2.605	2D	750	13" diameter paper tape and reel, anode towards the sprocket hole

**RATINGS AND CHARACTERISTICS CURVES**


( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)


Figure 1. Power Derating Curve




Figure 3. Pulse Waveform




Figure 2. Load Dump Power Characteristics  
(10 ms Exponential Waveform)


Figure 4. Reverse Power Capability




Figure 5. Typical Instantaneous Forward Characteristics




Figure 7. Typical Transient Thermal Impedance






Figure 6. Typical Reverse Characteristics

## PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





### Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.