







STRAIGHT SQUARE FLANGE JACK CRIMP TYPE - CABLE 5/50 D

PAGE 1/3 ISSUE 21-10-15H SERIES N PART NUMBER R161297000










	mm	
	Maxi	mini
A	16.3	16.1
В	3.3	3.2
C	18.35	18.15



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	NICKEL.
,		
Center contact	BERYLLIUM COPPER	GOLD OVER NICKEL
Outer contact	BRASS	NICKEL.
Insulator	PTFE	
Gasket	-	
Others parts	BRASS	NICKEL.
-	-	-
-	-	-



Technical Data Sheet

STRAIGHT SQUARE FLANGE JACK CRIMP TYPE - CABLE 5/50 D



PAGE **2/3** ISSUE 21-10-15H SERIES N PART NUMBER R161297000

PACKAGING

Standard	Contact us	Contact us
50	Contact us	Contact us

ELECTRICAL CHARACTERISTICS

Impedance 50 Frequency 0-3 GHz **VSWR** 1.15 0,0000 x F(GHz) Maxi 0.048 √F(GHz) dB Maxi Insertion loss RF leakage 101 - F(GHz)) dB Maxi - (Voltage rating Veff Maxi 850 Dielectric withstanding voltage 1500 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force - Mating End 27 N mini Axial force - Opposite end 27 N mini N.cm mini NA Torque

Recommended torque

Mating NA N.cm Panel nut NA N.cm Clamp nut N.cm 370 A/F clamp nut 12,0000 mm

Mating life 500 Cycles mini 40,8398 g

Weight

ENVIRONMENTAL

-55/+155 Operating temperature °С Hermetic seal NA Atm.cm3/s Panel leakage NA

SPECIFICATION

ASN-E0462 TC01 T 00

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	9	9	23	0	0	0

Assembly instruction:

Recommended cable(s)

KX 23 RG 142 FTX RG 142 BU RG 400 RG 223

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the

Cable retention

- pull off 200 N mini NA - torque N.cm

TOOLING

Part Number	Description	Hexagon
R282246000	CRIMPING DIES M22520/5-05	5.41
282291	CRIMPING TOOL M22520/1-01	2x4 (pos. 7)
282997	POSITIONER FOR TOOL 282.291(M22520/1-13)	rouge
R282293000	CRIMPING TOOL M22520/5-01	-
R282235011	CRIMPING DIES M22520/5-11	5.41
R282223000	CRIMPING TOOL	5.41

OTHER CHARACTERISTICS








PAGE **3/3**

ISSUE 21-10-15H

SERIES N


PART NUMBER R161297000

COMPONENTS



1


Slide onto the cable the heatshrink and the ferrule. Strip the cable.



2


Slide the clamp nut onto the crimp sleeve. Slide sub-assembly under the braid. Slide ferrule over the braid against clamp nut. (In direction F)

Crimp the ferrule with crimping tool + dies.



3


Cut the dielectric flush to crimp sleeve. Mount insulator against crimp sleeve.



4

Slide the centre contact onto the cable inner conductor against insulator.

Crimp centre contact with crimping tool and positioner.



heatshrink sleeve not shown

5

Screw sub-assembly into the connector body. (recommended coupling see connector TDS) Slide sleeve over ferrule and Heatshrink sleeve in place.

