


REVISION G

UNLESS OTHERWISE NOTED
 DIMENSIONS ARE IN INCHES
 TOLERANCES ARE:
 ONE PLACE DECIMALS $\pm .1$
 TWO PLACE DECIMALS $\pm .01$
 THREE PLACE DECIMALS $\pm .005$
 FOUR PLACE DECIMALS $\pm .0020$
 ANGLES
 $\pm 2^\circ$

TITLE:
 THRU-HOLE
 TERMINAL STRIP
 .018 DIA POST

DWG NO:
 TSF-1XX-01-XX-X-XX
 SHEET 1 OF 1

DO NOT SCALE
 FROM THIS PRINT



TSF-1XX-01-XX-X-XX

No. OF POSITIONS PER ROW
 -01 THRU -40 (SINGLE ROW)
 -01 THRU -36 (DOUBLE ROW)




LEAD STYLE
 -01: T-1RS7-01-X-2

PLATING SPECIFICATIONS
 -S: SELECTIVE (USE T-1RS7-01-R-2)
 -T: TIN (USE T-1RS7-01-T-2)
 -D: GOLD (USE T-1RS7-01-D-2)
 -SM: SELECTIVE GOLD / MATTE TIN TAIL (USE T-1RS7-01-SM-2)

POLARIZING OPTION
 POLARIZED POSITION
 SPECIFY OMITTED PIN

ROW SPECIFICATION
 -S: SINGLE ROW (USE TLW-40-S)
 -D: DOUBLE ROW (USE TLW-36-D)

CRITICAL DIMENSION INSPECTION TABLE	
ASSEMBLY OPERATION	IN-PROCESS INSPECTION
FILL T-1RS7-01-XX-2	C1, C2, C3
CUT TO POSITION	C4



- NOTES:
- 1.) TERMINAL PUSHOUT FORCE: 1 lbs MIN.
 - 2.) (C) REPRESENTS A CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL USE.
 - 3.) MAXIMUM CUT FLASH: .010
 - 4.) MAXIMUM FLASH ALLOWED IN THIS AREA: .020

C1-A,I-MV

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC INC. AND SHALL NOT BE REPRODUCED OR TRANSMITTED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC INC.

samtec

EXSPROD/ASSEMBLY/100
 TSF-ASM

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY: REIDINGER 11-23-92
 CHECKED BY: MCCARTIN

ENG. APPROVAL
 DEM

TSF-1XX-01-XX-X-XX
 SHEET 1 OF 1