

CLF10040-H TYPE SMD Power Inductor

Component Image & Dimension



Applications:

Automotive Appliance (ECM, HID, Air Bag, Transmission Control, Car Navigation, Car Audio, GPS System) etc.

Features:

a) Miniature Size:

Mount Area: 9.7mm x 10mm Low Profile: 4.1mm Max. Height

b) Tough Design

Generic use for Automotive Appliance.

Heat and vibration, mechanical shock resistance ability can endure an automobile use.

Operation temperature ; $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$

(Including self-temperature rise)

Storage temperature ; $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$

- c) High Magnetic Shield Construction should actualize High Resolution for EMC Protection.
- d) Automatic Mounting in Tape & Reel Package.

*Recommended Land Pattern (Unit: mm)



Electrical Specification (Ref.)

TDK-EPC Identification		Inductance		Test	DC Resistance		Rated DC Current	
		Spec. (uH)	Tol.	Freq. (kHz)	Spec. (Ohm.)	Tol.	Idc 1 (A)	Idc 2 (A)
CLF10040T-	1R0N-H	1.0	+/-30%	100	5.7m	+/-30%	12.0	6.3
CLF10040T-	1R5N-H	1.5	+/-30%	100	7.1m	+/-30%	10.6	5.8
CLF10040T-	2R2N-H	2.2	+/-30%	100	9.7m	+/-30%	7.5	5.0
CLF10040T-	<i>3R3N-H</i>	3.3	+/-30%	100	11.0m	+/-30%	6.6	4.8
CLF10040T-	4R7N-H	4.7	+/-30%	100	14.5m	+/-30%	5.4	4.2
CLF10040T-	6R8N-H	6.8	+/-30%	100	18.5m	+/-30%	4.8	3.7
CLF10040T-	100M-H	10	+/-20%	100	26m	+/-20%	4.0	3.3
CLF10040T-	150M-H	15	+/-20%	100	40m	+/-20%	3.2	2.5
CLF10040T-	220M-H	22	+/-20%	100	55m	+/-20%	2.7	2.2
CLF10040T-	330М-Н	33	+/-20%	100	80m	+/-20%	2.2	1.7
CLF10040T-	470M-H	47	+/-20%	100	125m	+/-20%	1.9	1.3
CLF10040T-	680M-H	68	+/-20%	100	180m	+/-20%	1.6	1.1
CLF10040T-	101M-H	100	+/-20%	100	0.24	+/-20%	1.3	1.0
CLF10040T-	151M-H	150	+/-20%	100	0.38	+/-20%	1.0	0.8
CLF10040T-	221М-Н	220	+/-20%	100	0.52	+/-20%	0.88	0.70
CLF10040T-	331М-Н	330	+/-20%	100	0.86	+/-20%	0.70	0.53
CLF10040T-	471M-H	470	+/-20%	100	1.21	+/-20%	0.56	0.44

Note) Idc 1: Depend on the Inductance Saturation. (-10% Saturation from Initial L Value)

Idc 2: Depend on the self temperature rise. (+30 degC typ.)

