


IEC Appliance Outlet B, Screw-on Mounting, Front Side, Solder Terminal

**Description**

- Panel Mount:
- Screw-on mounting, Frontside
- Connector, Pin temperature 70 °C, protection class I or II
- Solder terminal

Approvals

- VDE Certificate Number: 115734
- UL File Number: E57445
- CSA File Number: 27324


References**Weblinks**

[pdf](#), [General Product Information](#), [Approvals](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Store](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

Technical Data

Ratings IEC	2.5 A / 250 VAC; 50 Hz
Ratings UL/CSA	2.5 A / 250 VAC; 60 Hz
Dielectric Strength	> 4 kVAC between L-N > 2 kVAC between L/N-PE (1 min/50 Hz)
Allowable Operation Temp.	-25 °C to 70 °C
Degree of Protection	from front side IP 20 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class 1 or 2 acc. to IEC 61140
Terminal	Solder terminals
Material: Housing	PA6, black / grey / white, UL 94V-0

Appliance Outlet	B acc. to IEC/EN 60320-2-2 UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 2.5 A, Protection Class 1 or 2
------------------	--

Dimensions

Length of the terminal please find at the order code configuration table

Config. Code

5888 - H - A B C 0 - D - E O

The characters are placeholders for the correspondingly keys of selections from the key tables.

5888 - H - A B C 0 - D - E O = Type

Type	Configuration key
protection class 2	B
protection class 1	X

5888 - H - A B C 0 - D - E O = Terminals

Terminal L	Configuration key
solder terminal 	1

5888 - H - A B C 0 - D - E O = Terminals

Terminal N	Configuration key
solder terminal	1

Symbols similar as in table A

5888 - H - A B C 0 - D - E O = Terminals

Terminal Ground	Configuration key
without terminal	0
solder terminal	1

Symbols similar as in table A

5888 - H - A B C 0 - D - E O = Color

Color	Configuration key
jet black; RAL9005	A
silver grey; RAL7001	B
pure white; RAL9010	D

5888 - H - A B C 0 - D - E O = Style

Style	Configuration key
flange with countersunk holes	1
flange with through holes	2

5888 - H - A B C 0 - D - E O = Features

Features	Configuration key

Variants

Config. Code	Description	Order Number
5888-X-1110-A-1	5888, IEC Connector B, 70°C, version: 1 or 2, L: solder terminal, N: solder terminal, ground: solder terminal, color: jet black; RAL9005, design: flange with countersunk holes, dimension X:	6180.0008

The listed variants should be available from stock. Other versions on request www.schurter.com/contact

Packaging unit

50 Pcs

Mating Inlets/Plugs

Category / Description

[Interconnection Cord Overview complete](#)

Interconnection Cord with IEC Plug A, Angled

2705

[Interconnection Cord further types to 5888](#)