





MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



MOUNTING HARDWARE



NOTES:

1. OPERATING TEMPERATURE RANGE: -55°C TO +125°C.
2. SILVER PLATED CASE, LEAD AND MOUNTING HARDWARE.
3. MAX. RECOMMENDED MOUNTING TORQUE : 2.0 lb. - in.
4. MAX. RECOMMENDED SOLDERING TEMPERATURE : 260°C.
SEE INSTALLATION RECOMMENDATIONS.
5. NUT AND LOCKWASHER INCLUDED.
6. TUSONIX STANDARD PART NUMBER: 4403-031.
TUSONIX RoHS COMPLIANT PART NUMBER: 4403-031 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
7. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

500	GMV	300	200	10	10 G Ω	500 VDC	----	----	15	35	40
CAP.(pf)	TOLERANCE	85 °C	125 °C	DC CURRENT (AMPS)	IR @ 100 VDC	D.W.V.	1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
		DC WORKING VOLTAGE					MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220				

REVISION RECORD	Original Release	0	20080121-2-02		--TOLERANCES-- Unless Otherwise Specified	Title MINIATURE BUSHING STYLE EMI FILTER	
	C.O. 20020509-5-01				DECIMAL ± NOTED		
	REVISED NOTE 6 & ADDED NOTE 7, S.M. 01-22-08				ANGLES ± NOTED	Drawn L.E. 05-09-02	Scale 8 X
					TUSONIX TUCSON, ARIZONA	Approved T.C. 05-09-02	
						A	4403-031