




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

1. SUPPLIED WITH SILVER PLATED HEX NUT AND INTERNAL TOOTH LOCK WASHER.
2. MOUNTING TORQUE NOT TO EXCEED 5 lb - in. MAX. [.565 N-m]
3. TUSONIX STANDARD PART
NUMBER: 2425-018-X5U0-102M.
TUSONIX RoHS COMPLIANT PART
NUMBER: 2425-018-X5U0-102M LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
4. PART MARKING: STANDARD: BLACK INK FOR TRADEMARK AND CAP. CODE.
RoHS PART: GREEN FOR TRADEMARK AND CAP. CODE.

SPECIFICATIONS

Tusonix Style:	2425-018
Capacitance Value:	1000 pF
Capacitance Tolerance:	±20 %
Temp. Characteristic:	X5U
Rating:	200 VDC @ + 85°C / 100 VDC @ +125°C
Current (A):	20
Operating Range:	-55°C TO +125°C
Insulation Resistance:	10,000 megohms (min.) @ +25°C
DWV @ 2 Sec. Min:	600 VDC

REVISION RECORD				--TOLERANCES-- Unless Otherwise Specified		Title MINIATURE BUSHING FEED-THRU	
Original Release C.O. 20010816-1-01	0	NOTE 2 REVISED. ADDED NUT & WASHER. S.M. 09-13-01		DECIMAL ± .031 [0.79]		Drawn S.M. 08-16-01	
20010913-4-02	1	TUSONIX STYLE CURRENT (A), INSULATION RESISTANCE, DWV COLUMNS & NOTE 2 REVISED L.E. 05-25-04		ANGLES ± 		Approved T.C. 08-16-01	
20040514-3-07	2	ADDED NOTES 3 & 4. S.M. 11-01-05		TUSONIX TUCSON, ARIZONA		A	2425-018-X5U0-102M
20051031-1-10	3						