




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



SPECIFICATIONS

CAP. VALUE	1000 pF
CAP. TOL.	±20%
TEMP. CHAR.	X5U
OPERATING TEMP.	-55° TO +125°C
OPERATING VOLT.	200 WVDC @ +85 °C
DIELECTRIC WITHSTANDING	400 VDC, 2 SEC.

NOTES:

- TUSONIX STANDARD PART NUMBER: 2463-002-X5U0-102M.
 TUSONIX RoHS COMPLIANT PART
 NUMBER: 2463-002-X5U0-102M LF.
 CUSTOMER MUST SPECIFY STANDARD OR RoHS PART
 NUMBER WHEN ORDERING.
- PART MARKING: STANDARD PART, NO MARKING.
 RoHS PART: GREEN LABELING ON PACKAGING.

X-2015 Rev-0

REVISION RECORD

Original Release
 C.O. 20070108-1-01

--TOLERANCES--
 Unless Otherwise Specified

DECIMAL ± .031 [0.79]

ANGLES ±

TUSONIX
 TUCSON, ARIZONA

Title

**SHOULDER
 FEED-THRU**

Drawn S.M. 01-08-07

Scale 7X

Approved R.L. 01-08-07

A 2463-002-X5U0-102M