


DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



1. SUPPLIED WITH SILVER PLATED
HEX NUT AND LOCKWASHER.
2. TUSONIX STANDARD PART NUMBER: 4201-006.
TUSONIX RoHS COMPLIANT PART NUMBER: 4201-006 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
3. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
4. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT (Idc)	DWV (VDC)	I.R. MIN. @ 100 VDC	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
1500	200	100	15 A	400	10 G	5	38	63	70

REVISION RECORD Original Release C.O. 3173 RDN TO COMP FMT & ADDED METRIC, 02-11-02		0	--TOLERANCES-- Unless Otherwise Specified DECIMAL ±  ANGLES ±  TUSONIX TUCSON, ARIZONA	Title BUSHING STYLE EMI FILTER	
20020213-3-02 ADDED NOTES. S.M. 07-27-05		1		Drawn S.M. 01-11-02	Scale 4 X
20050726-2-15		2		Approved T.C. 02-11-02	
				A	4201-006