


Wire &amp; Cable &gt; Hook Up Wire

Cable Type: **Spec 55**Voltage Rating: **600 V**Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**Conductor Material: **Nickel-Coated Copper**Wire Size: **22 AWG**

## Features

### Product Type Features

Cable Style	Primary
Product Type	Wire
Product Classification	High Performance - Spec 44, 55 & RCW
Cable Type	Spec 55

### Configuration Features

Number of Conductors	1
Number of Strands	19

### Electrical Characteristics

Voltage Rating	600 V
----------------	-------

### Body Features

Wire Color	White
Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Conductor Material	Nickel-Coated Copper

### Dimensions

	.0455 in
Strand Size	34 AWG
Wire Size	22 AWG

### Usage Conditions

Operating Temperature Range

-65 – 200 °C

## Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer






This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # D17660-000  
D-200-82

## Customers Also Bought

TE Part #1617761-7  
FCB-405-CX4TE Part #349799-000  
55PC0213-14-9TE Part #CA3265-000  
55PC0213-22-2LTE Part #EK0855-000  
55PC0213-26-9TE Part #EG4523-000  
55PC0223-18-9/96TE Part #EG4524-000  
55PC0223-20-9/96TE Part #EK0894-000  
55PC0226-26-9/96TE Part #EG6363-000  
55PC6306-14-9/93/96-9TE Part #YDTS20W13-  
35SBV001  
RECP ASSYTE Part #YDTS26W17-  
06PAV001  
PLUG ASSY

## Documents

### Product Drawings 55PC0213-22-9

English

---

### Datasheets & Catalog Pages 1654025\_Sec9\_SPEC55

English

---

### Product Specifications Product Specification

English