



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Cable Clamp**

Number of Positions: **9**

Shielded: **No**

Sealable: **No**

Features

Product Type Features

D-Shaped Connector Accessories	Cable Clamp
Sealable	No

Configuration Features

Number of Positions	9
---------------------	---

Operation/Application

Shielded	No
----------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2015 (163) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Model / Part # 4-1393560-6
V42254A4000D 25=SUB D BUEGEL




TE Model / Part # 749619-4
SZ1 STRAIN RELIEF CLIP,ZINC


Customers Also Bought




TE Model / Part #4-1393560-6
V42254A4000D 25=SUB D BUEGEL




TE Model / Part #2-1393531-6
V23535A3280C101=BKMOD422 FEDER




TE Model / Part #926209-4
2X4P LOCK-CLIP GEH




TE Model / Part #1857211-1
KIT, SCREW RETAINER AMPLIMITE,




TE Model / Part #3-1393531-4
V23535A3280C341=BKMOD422 FEDER



TE Model / Part #87190-1
LOCKING CLIP CONT ASSY .025 SQ



TE Model / Part #926329-1
KEYING PLUG



TE Model / Part #926209-6
2X6P LOCK-CLIP GEH



TE Model / Part #926899-3
[UNIV-MNL SPLIT ST](#)



TE Model / Part #926209-3
[LOCKING CLIP HSG.](#)

Documents

Product Drawings

[V42254A4000D 9=SUB D BUEGEL](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_4-1393560-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1393560-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1393560-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.