

0.5/1.5 38POS CAP ASSY DIP BOARD LOCK

✓ ACTIVE

0.50 Connector System

TE Part # 1903876-1


TE Internal #: 1903876-1

LOW & MEDIUM POWER HEADER

[View on TE.com >](#)



Connectors > Automotive, Truck, Bus, & Off-Road Connectors > PCB Headers > LOW & MEDIUM POWER HEADER



Number of Positions: 38

Centerline (Pitch): 1.6 mm, 1.8 mm, 3.2 mm, 3.6 mm [ .063 in, .071 in, .126 in, .142 in ]

Sealable: No

Mounting Orientation: Horizontal/90°

Number of Rows: 3

[All LOW & MEDIUM POWER HEADER \(188\)](#)

Features

Product Type Features

Hybrid Header	Yes
Shielded	No
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Sections	1
Number of Signal Positions	38
Number of Positions	38
Number of Rows	3

Electrical Characteristics

Voltage Rating (Max)	12 VDC
Operating Voltage	12 VDC
Nominal Voltage Architecture	12 V

Body Features

Color	Natural
-------	---------

Contact Features

Tab Width	.5 mm, 1.5 mm[.02 in][.059 in]
-----------	--------------------------------

0.5/1.5 38POS CAP ASSY DIP BOARD LOCK

TE Part # 1903876-1  
TE Internal #: 1903876-1



Tab Thickness	.4 mm, .64 mm[.016 in][.025 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method	Through Hole - Solder
--------------------	-----------------------

Mechanical Attachment

Locking Interface	With
PCB Mount Alignment	Without
Mounting Holes	With
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Mounting Orientation	Horizontal/90°

Housing Features

Centerline (Pitch)	1.6 mm, 1.8 mm, 3.2 mm, 3.6 mm[.063 in][.071 in][.126 in][.142 in]
--------------------	--

Dimensions

Length	33.7 mm[1.326 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Profile Height from PCB	11.8 mm[.465 in]
Width	40.3 mm[1.587 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C[149 °F][158 °F][167 °F][176 °F][185 °F]
Operating Temperature Range	-30 – 85 °C[-22 – 185 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	None
------------------------	------

Packaging Features

Packaging Type	Tube
----------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | 0.50 Connector System

0.5/1.5 38POS CAP ASSY DIP BOARD LOCK

TE Part # 1903876-1  
TE Internal #: 1903876-1



Automotive Seals & Cavity Plugs(2)



Automotive, Truck, Bus, & Off-Road Headers(17)



Automotive, Truck, Bus, & Off-Road Housings(31)




Automotive, Truck, Bus, & Off-Road Terminals(9)


Customers Also Bought




TE Part #1473369-9  
SQUIB 11DIA SCR ASSY  
8.8MM TYPE



TE Part #175978-1  
CAP HOUSING 187 (4.8  
MM) ASSEMBLY



TE Part #178025-2  
FF 250 CAP HSG DBL 6P  
BLACK



TE Part #353842-1  
FPC SENSOR CONT.

Documents

Product Drawings

0.5/1.5 38POS CAP ASSY DIP BOARD LOCK

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1903876-1\_E.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1903876-1\_E.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1903876-1\_E.3d\_stp.zip

English

Product Specifications

Product Specification

Japanese

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

0.5/1.5 38POS CAP ASSY DIP BOARD LOCK

TE Part # 1903876-1  
TE Internal #: 1903876-1



Instruction Sheet (non U.S.)

English