


[Home](#) > [Products](#) > [Wire & Cable](#) > [Product Feature Selector](#) > Product Details

55A0114-30-9 Product Details

 [Share](#)

 [Print](#)

 [Email](#)



55A0114-30-9

TE Internal Number: 216175-000

 [Active](#)

Spec 44, Spec 55 and Spec RCW Wire and Cable

 [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 30 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information	
Product Drawings: • WIRE, RADIATION-CROSSLINKED, MODIFIED, ETFE-INSULATE... (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available List all Documents	Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Cable Type = Spec 55 • Cable Style = Primary Electrical Characteristics: • Voltage Rating (VAC) = 600 Dimensions: • Conductor Outer Diameter (mm [in]) = 0.31 [0.012] Body Features: • Wire Size (AWG/CM) = 30 AWG • Conductor Type = Silver-Coated High-Strength Copper Alloy • Wire Color = White • Nominal Outside Diameter (mm [in]) = 0.61 [0.024] • Wire Diameter (mm [in]) = 0.61 [0.024] Configuration Features: • Number of Conductors = 1	Industry Standards: • Government/Industry Qualification = No • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Converted to comply with RoHS directive Conditions for Usage: • Temperature Range (°C) = -65 – +200 • Wire Size - Details = 30 AWG 0.057 mm², 0.00009 in², 7 x 38 AWG Operation/Application: • Application = General Purpose - Lightweight Packaging Features: • Wire Source = United States Other: • Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



Feedback

