



Wire & Cable > Hook Up Wire



Cable Type: **MIL-DTL-22759**
Voltage Rating: **600 V**
Wire Color: **White**
Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**
Conductor Material: **Tin-Coated Copper**

Features

Product Type Features

Cable Style	Primary
Product Type	Cable
Product Classification	Cable - High Performance - Spec 44, 55 & RCW
Cable Type	MIL-DTL-22759

Configuration Features

Number of Conductors	1
Number of Strands	19

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Wire Color	White
Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Conductor Material	Tin-Coated Copper

Dimensions

Overall Outside Diameter	1.96 mm[.077 in]
Wire Diameter	1.96 mm[.077 in]



Conductor Diameter	1.42 mm[.056 in]
	.009 in
Strand Size	29 AWG
Wire Size	16 AWG

Usage Conditions

Operating Temperature Range	-65 – 150 °C
-----------------------------	--------------

Other

Wire Source	United States
-------------	---------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Model / Part # 650076-000


D-436-38

Customers Also Bought




TE Model / Part #255111-000

55A1811-22-9-9CS2275




TE Model / Part #218205-001

22759/34-18-9




TE Model / Part #913237-000

55A1811-20-9-9CS2275



TE Model / Part #074911-000

55A1821-20-9/96-9CS2275




TE Model / Part #644807-000

55A1121-22-9/96-9CS2275




TE Model / Part #2560-215-1631L

CONT PIN




TE Model / Part #702841-000

55A1821-22-9/96-9CS2275



TE Model / Part #218204-001

22759/34-20-9



TE Model / Part #218203-002

22759/34-22-9



TE Model / Part #2560-201-2031L

CONT PIN

Documents

Product Drawings

22759/34-16-9

English

Datasheets & Catalog Pages

1654025_Sec9_SPEC55

English

Raychem Wire and Cable Quick Reference Guide

English



Product Specifications

Product Specification

English