

## 3M™ Double Coated Tapes 442F, 442KW, 442W, 442DL

### Product Description

3M™ Double Coated Tape 442F, 442KW, 442W, and 442DL with 3M™ Adhesive 830. These double coated film tapes feature a thin polyester film carrier for dimensional stability and improved handling with ease of die cutting and laminating. 3M™ Adhesive 830 is a firm rubber adhesive system that provides a combination of high shear strength, good temperature performance, good solvent resistance and good quick stick to a wide variety of materials as well as clean removability from many surfaces.

### Key Features

- The polyester liner offers moisture stability.
- The polyester film carrier enhances the workability when laminating to various types of surfaces.
- The film carrier also enhances the die cutability of the finished product.
- Provides clean removability from many surfaces.

### Product Construction/Material Description

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

3M™ Double Coated Tape 442F, 442KW, 442W, 442DL				
Property	Value			
	3M™ tape 442F	3M™ tape 442KW	3M™ tape 442W	3M™ tape 442DL
Adhesive	3M™ Adhesive 830			
Adhesive Thickness (Face side)	0.038mm (1.5 mil)			
Adhesive PET Carrier	0.025mm (1.0 mil)			
Adhesive Thickness (Back side)	0.038mm (1.5 mil)			
Adhesive Thickness (without liner)	0.10mm (4.0 mil)			
Release Liner Primary Liner Thickness	Polyester Film 0.07mm (3.0 mil)	Polycoated Paper 0.11mm (4.5 mil)	Polycoated Paper 0.11mm (4.5 mil)	Polycoated Paper 0.11mm (4.5 mil)
Release Liner Secondary Liner Thickness	NA	NA	NA	Polyester Film 0.05mm (2.0 mil)
Release Liner Color	Translucent	Off-White	Off-White	Off-White/Translucent

### Applications

These tapes are ideal for bonding together a wide variety of similar and dissimilar materials such as rubbers, metals, glass, papers, paints and many plastics. Some application ideas include:

- Splicing of films, foils, papers, fabrics.
- Holding objects where high shear forces are encountered.
- Holding grinding and polishing pads.
- Miscellaneous joining and holding uses.

### Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improves bond strength.

To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.

# 3M™ Double Coated Tapes 442F, 442KW, 442W, 442DL

Note: Carefully read and follow the manufacturer's precautions and directions for use when working with solvents. These cleaning recommendations may not be in compliance with the rules of certain Air Quality Management Districts in California; consult applicable rules before use.

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm for good adhesion. However, once properly applied, low temperature holding is generally satisfactory.

## Typical Physical Properties and Performance Characteristics

**Note:** The following technical information and data should be considered representative or typical only and should not be used for specification purposes. Final product specifications and testing methods will be outlined in the products Certificate of Analysis (COA) that is shipped with the commercialized product.

3M™ Double Coated Tape 442F, 442KW, 442W, 442DL					
Property		Method <sup>1</sup>		Value	
180 Degree Peel Adhesion @ 72-hour dwell <sup>2</sup>	Test Method ASTM D3330	oz/in	N/mm	kg/25.4mm	
		SS 70	0.78	1.96	
90 Degree Peel Adhesion @ 15-minute dwell <sup>2</sup>	Test Method ASTM D3330	oz/in	N/mm	kg/25.4mm	
		SS 53	0.59	1.49	
90 Degree Peel Adhesion @ 72-hour dwell <sup>2</sup>	Test Method ASTM D3330	oz/in	N/mm	kg/25.4mm	
		SS 56	0.63	1.57	
		PC 53	0.59	1.49	
		ABS 52	0.58	1.46	
		PP 40	0.45	1.12	
Static Shear 1000g RT 500g at 70C	Test Method ASTM D3654				
Relative High Temperature Operating Range	3M Test Method Long Term Short Term	<10,000 Minutes			
		<10,000 Minutes			
		150F (66C)			
		180F (82C)			

<sup>1</sup>Methods listed as ASTM are tested in accordance with the ASTM method noted

<sup>2</sup>Peel tests were completed with 2 mil Al foil backing

## Storage and Shelf Life

The self-life of 3M™ Double Coated Tapes 442F, 442KW, 442W, and 442DL is 18 months from date of manufacture when stored in original packaging materials and stored at 70°F (21°C) and 50% relative humidity.

## Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is commercially available from 3M. The commercially available product will have a COA specification established. The COA contains the 3M specifications and test methods for the products performance limits that the product will be supplied against. The 3M product is supplied to 3M COA test specifications and the COA test methods. Contact your local 3M representative for this product's COA.

This technical data sheet may contain preliminary data and may not match the COA specification limits and/or test methods that may be used for COA purposes.

Final product specifications and testing methods will be outlined in the products Certificate of Analysis (COA) that is shipped with the commercialized product.

# 3M™ Double Coated Tapes 442F, 442KW, 442W, 442DL

**Regulatory:** For regulatory information about this product, contact your 3M representative.

**Technical Information:** The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

**Product Use:** Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

**Warranty, Limited Remedy, and Disclaimer:** Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



## Electronics Materials Solutions Division

3M Center, Building 224-3N-11

St. Paul, MN 55144-1000

1-800-251-8634 phone

651-778-4244 fax

[www.3M.com/electronics](http://www.3M.com/electronics)

3M is a trademark of 3M Company.

Please recycle.

©3M 2019. All rights reserved.

60-5005-0146-9

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7100168544](#) [7100170668](#) [7100171703](#) [7100171704](#) [7100171705](#) [7100171713](#) [7100174124](#)