

Power SMD LED CLCC-6 Warm White



DESCRIPTION


The VLMW611. is one of the most robust and light efficient LEDs in the market. Its ceramic package makes it the ideal light source in applications of high thermal considerations allowing the additional current drive for a maximum light output while maintaining a high service life of up to 50K h. The reflector inside this package is filled with a mixture of silicone and TAG phosphor. The TAG phosphor converts the blue emission partially to yellow, which mixes with the remaining blue to white.

PRODUCT GROUP AND PACKAGE DATA

Product group: LED
Package: SMD CLCC-6
Product series: power
Angle of half intensity: ± 60°

FEATURES

Utilizing InGaN technology





- · Luminous intensity and color grouping
- Luminous intensity ratio per package unit $I_{Vmax}/I_{Vmin} \le 1.6$
- ESD-withstand voltage: up to 1 kV according to JESD22-A114-B
- Compatible with IR reflow solder processes according to CECC 00802 and J-STD-020C
- · Lead (Pb)-free device
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC
- Preconditioning: acc. to JEDEC level 4
- Automotive qualified AEC-Q101

APPLICATIONS

- · Camera flash light
- Interior and exterior automotive lighting: brake lights, backlighting, side markers
- · Indicator lighting
- · Signal and symbol luminaire
- · Marker lights

PARTS TABLE					
PART	COLOR, LUMINOUS INTENSITY (at $I_F = 140 \text{ mA}$)	LUMINOUS FLUX (TYP.)	TECHNOLOGY		
VLMW611BADAK3L5-08	Warm white, I _V = (1800 to 5600) mcd	10 lm	InGaN/TAG		
VLMW611BADAK3L5-18	Warm white, $I_V = (1800 \text{ to } 5600) \text{ mcd}$	10 lm	InGaN/TAG		
VLMW611CADBK3L5-08	Warm white, I _V = (2800 to 7100) mcd	13 lm	InGaN/TAG		
VLMW611CADBK3L5-18	Warm white, I _V = (2800 to 7100) mcd	13 lm	InGaN/TAG		



ABSOLUTE MAXIMUM RATINGS ¹⁾ VLMW611.					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Forward current		I _F	150	mA	
Power dissipation		P _{tot}	650	mW	
Junction temperature		T _j	+ 125	°C	
Surge current $T_j < 400 \text{ ms, d} = 0.3, T_j < 65 ^{\circ}\text{C}$			350	mA	
Operating temperature range		T _{amb}	- 40 to + 100	°C	
Storage temperature range		T _{stg}	- 40 to + 100	°C	
Thermal resistance junction/pin	Metal core pcb 960 mm ² per LED	R _{thJP}	50	K/W	
Thermal resistance junction/ambient	Metal core pcb 900 mm- per LED	R _{thJA}	100	K/W	

Note:

Not designed for reverse operation

¹⁾ T_{amb} = 25 °C, unless otherwise specified

OPTICAL AND ELECTRICAL CHARACTERISTICS ¹⁾ VLMW611., WARM WHITE							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luncia que internetto	I _F = 140 mA	VLMW611BADA	I _V	1800		5600	mcd
Luminous intensity		VLMW611CADB	I _V	2800		7100	mcd
Luminous flux	I _F = 140 mA	VLMW611BADA	φV	5400		16800	mlm
calculated ³⁾		VLMW611CADB	φV	8700		22300	mlm
Chromaticity coordinate x acc. to CIE 1931	I _F = 140 mA		х		0.40		
Chromaticity coordinate y acc. to CIE 1931	I _F = 140 mA		у		0.39		
Angle of half intensity	I _F = 140 mA		φ		± 60		deg
Forward voltage ²⁾	I _F = 140 mA		V _F	2.9	3.3	4.3	V
Temperature coefficient of V _F	I _F = 140 mA		TC _{VF}		- 3		mV/K
Temperature coefficient of I _V	I _F = 140 mA		TC _{IV}		- 0.4		%/K

Note:

Not designed for reverse operation

³⁾ Theoretical correlation for 120° emission angle

LUMINOUS INTENSITY/FLUX CLASSIFICATION WARM WHITE		
GROUP	LUMINOUS INTENSITY I _V (MCD)	
STANDARD	MIN.	MAX.
BA	1800	2240
BB	2240	2800
CA	2800	3550
СВ	3550	4500
DA	4500	5600
DB	5600	7100
EA	7100	9000

Note:

Luminous intensity is tested at a current pulse duration of 25 ms and an accuracy of \pm 11 %.

The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each reel (there will be no mixing of two groups on each reel).

In order to ensure availability, single brightness groups will not be orderable.

In a similar manner for colors where wavelength groups are measured and binned, each single wavelength group is packed in a single reel. In order to ensure availability, single wavelength groups can not be ordered.

¹⁾ $T_{amb} = 25$ °C, unless otherwise specified 2) Forward voltages are tested at a current pulse duration of 1 ms and a tolerance of \pm 0.05 V





ROMATICITY COORDINATED GROUPS FOR WARM WHITE SMD LED		
	X	Y
	0.373	0.350
К3	0.387	0.358
K3	0.393	0.376
	0.378	0.368
	0.378	0.368
K4	0.393	0.376
K4	0.399	0.395
	0.383	0.386
	0.383	0.386
K5	0.399	0.395
K5	0.405	0.412
	0.388	0.403
	0.387	0.358
L3	0.400	0.366
L3	0.407	0.384
	0.393	0.376
	0.393	0.376
1.4	0.407	0.384
L4	0.414	0.402
	0.399	0.395
	0.399	0.395
1.5	0.414	0.402
L5	0.421	0.420
	0.405	0.412

Note:

Chromaticity coordinate groups are tested at a current pulse duration of 25 ms and a tolerance of ± 0.01.

CROSSING TABLE			
VISHAY	OSRAM		
VLMW611.	LCW6SP		

TYPICAL CHARACTERISTICS

T_{amb} = 25 °C, unless otherwise specified




Figure 1. Forward Current vs. Ambient Temperature




Figure 2. Relative Spectrale Emission






Figure 3. Relative Luminous Intensity vs. Forward Current




Figure 4. Coordinates of Color Groups




Figure 5. Relative Luminous Flux vs. Ambient Temperature




Figure 6. Forward Current vs. Forward Voltage




Figure 7. Forward Voltage vs. Ambient Temperature




Figure 8. Color Coordinate vs. Ambient Temperature










Figure 9. X, Y Coordinate vs. Forward Current

TAPING DIMENSIONS in millimeters



VISHAY.

PACKAGE DIMENSIONS in millimeters




Issue: 2; 07.05.07

20672

SOLDERING PADS DIMENSIONS in millimeters

SOLDERING PROFILE



Drawing refers to following types: LA G67F Soldering pads

Drawing-No.: 6.581-5006.01-4 Issue: 1; 07.02.07

ISSUE: 1; 07.02.07 20598





Figure 10. Vishay Lead (Pb)-free Reflow Soldering Profile (acc. to J-STD-020C)



BAR CODE PRODUCT LABEL EXAMPLE:




- A) Type of component
- B) Manufacturing plant
- C) SEL selection code (bin):

e.g.: BA = code for luminous intensity group K3 = code for chromatisity coordinate

- D) Date code year/week
- E) Day code (e.g. 2: Tuesday)
- F) Batch no.
- G) Total quantity
- H) Company code

DRY PACKING

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



FINAL PACKING

The sealed reel is packed into a cardboard box. A secondary cardboard box is used for shipping purposes.

Vishay Semiconductors

RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the aluminum bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.

After more than 72 h under these conditions moisture content will be too high for reflow soldering.


In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

192 h at $40 \,^{\circ}\text{C} + 5 \,^{\circ}\text{C/-} \, 0 \,^{\circ}\text{C}$ and $< 5 \,^{\circ}\text{KH}$ (dry air/nitrogen) or

96 h at 60 $^{\circ}$ C + 5 $^{\circ}$ C and < 5 $^{\circ}$ RH for all device containers or

24 h at 100 °C + 5 °C not suitable for reel or tubes.

An EIA JEDEC standard JESD22-A112 level 4 label is included on all aluminum dry bags.



Example of JESD22-A112 level 4 label

ESD PRECAUTION

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the antistatic shielding bag. Electro-static sensitive devices warning labels are on the packaging.

VISHAY SEMICONDUCTORS STANDARD BAR CODE LABELS

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.



OZONE DEPLETING SUBSTANCES POLICY STATEMENT

It is the policy of Vishay Semiconductor GmbH to

- 1. Meet all present and future national and international statutory requirements.
- 2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

- 1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
- 2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
- 3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

The IEC/EN standards require that the desired classification Accessible Emission Limit shall not be exceeded in "Normal" and "Single Fault Conditions". This product is in Compliance with the requirement in CEN/IEC/EN60825-1 to ensure that required classifications are not exceeded in single fault conditions.

> We reserve the right to make changes to improve technical design and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany

www.vishav.com **Document Number 81783** Rev. 1.1, 11-Dec-07

Legal Disclaimer Notice



Vishay

Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Document Number: 91000
Revision: 08-Apr-05
www.vishay.com