

## APPROVAL SHEET

# WLPN606045 Series Shielded SMD Power Inductors

\*Contents in this sheet are subject to change without prior notice.



### **Features**


- 1. Close magnetic loop with magnetic resin shielded.
- 2. Low profile, High inductance.

## **Applications**

- 1. General propose power inductor in DC power system.
- 2. Inductor in DC/DC converter.
- 3. Low profile for portable and wearable device.
- 4. LC filter in Audio D class Amplifier.

### **Shape and Dimension**

Unit: mm



## **Ordering Information**

WL	PN	6060	45	N	1R5	L	В	
Product Code	Series	Dimensions	Thickness	Tolerance	Value	Packing Code		
WL: Inductor	Shielded SMD Power Inductors	6.0 * 6.0 mm	4.5 mm	M: ± 20% N: ± 30%	1R5 = 1.5uH 150 = 15uH. 101=100uH	L=13" Reeled (Embossed Tape)	B:STD	



#### **Electrical Characteristics**

WLPN606045	MARK	1 ()	Inductance	Test Freq	DCR	Irms	Isat
Series	WANK	L (uH)	Tolerance	(KHz)1V	(mΩ)	(A)	(A)
WLPN606045_1R0LB	1R0	1.0	N	100	18.2	6.00	8.50
WLPN606045 1R3LB	1R3	1.3	N	100	20.8	5.20	8.00
WLPN606045 1R5LB	1R5	1.5	N	100	23.4	5.00	8.00
WLPN606045 1R8LB	1R8	1.8	N	100	23.4	5.00	7.00
WLPN606045 2R2LB	2R2	2.2	N	100	27.3	4.50	6.00
WLPN606045 2R3LB	2R3	2.3	N	100	27.3	4.50	6.00
WLPN606045 3R0LB	3R0	3.0	N	100	31.2	4.00	5.00
WLPN606045 3R3LB	3R3	3.3	N	100	31.2	4.00	5.00
WLPN606045_4R5LB	4R5	4.5	M	100	40.3	3.70	4.00
WLPN606045_4R7LB	4R7	4.7	M	100	40.3	3.70	4.00
WLPN606045_6R3LB	6R3	6.3	M	100	49.4	3.50	3.80
WLPN606045 6R8LB	6R8	6.8	M	100	49.4	3.50	3.80
WLPN606045_100LB	100	10.0	M	100	61.1	2.80	3.00
WLPN606045_150LB	150	15.0	近有M 個	100	100.1	2.30	2.30
WLPN606045 220LB	220	22.0	N/M/	100	149.5	1.70	1.90
WLPN606045_330LB	330	33.0	、牧型M区有	100	188.5	1.50	1.50
WLPN606045_470LB	470	47.0	M	100	286.0	1.30	1.30
WLPN606045_680LB	680	68.0	M	100	429.0	1.00	1.00
WLPN606045_820LB	820	82.0		100	533.0	0.90	0.90
WLPN606045_101LB	101	100.0	SIVE SYSMEM ALLIA	100	650.0	0.80	0.80
WLPN606045_151LB	151	150.0	M	100	580.0	0.80	0.70

- 1. Test Frequency: 100KHz, 1V
- 2. Test Equipment:


Inductance: Chroma3302+1320+16502 or equivalent.

SRF:HP-4291B or equivalent. RDC:CH16502BC or equivalent.

- 3. Isat:Based on inductance decrease 30% Max.(at 20°C)
- 4. Irms:Based on temperature increase 40°C Max.(at 20°C)
- 5. Operating Temperature Range:-25 $^{\circ}$ C to +120 $^{\circ}$ C (Including self-temperature rise).
- 6. Storage Temp. Range : -40 $^{\circ}$ C to +85 $^{\circ}$ C.
- 7. MSL: Level 1.



## **Reflow Profile Chart (Reference):**





### **RELIABILITY PERFORMANCE**

Reliability Experiment For Electrical


Test Item	Test Item Test Condition	
Humidity Test	+40 $^{\circ}$ ± 2 $^{\circ}$ , humidity of 90% ± 5% (total 96 hours).	MIL-STD-202G Method 103B Test Condition B
High Temperature Test	1.Temperature: +125°C±2°C 2.Test time: 48±2hrs	IEC 68-2 Test Condition B
Low Temperature Test	1.Temperature: -40°C±2°C 2.Test time: 48±2hrs	IEC 68-2 Test Condition A
Thermal Shock	+125 $^{\circ}$ C±5 $^{\circ}$ C (30 minutes) ~ -40 ± 5 $^{\circ}$ C (30 minutes), temperature switch time: 5 minutes (total 50 cycles).	MIL-STD-202G Method 107G Test Condition B- 2
Life Test	+70℃±5℃ (250Hours)	MIL-STD-202G Method 108A Test Condition B

Reliability Experiment For Physical

Test Item	Test Condition	Standard Source
Vibration Test	10-55-10HZ, amplitude: 1.5mm, direction: X, Y, Z axes, each axis 2 hours (total 6 hours).	MIL-STD-202G Method 201A
Solder Heat Resistance Test	IR/convection reflow:Peak Temp 250±5℃ for 5Sec in air, Through 2 Cycle. Temperature Ramp:+1~4℃/sec; Above1 83℃, must keep 90 s - 120 s	MIL-STD-202G Method 210F Test Condition (Reflow)
Solder Ability Test	Soak in 245 $^{\circ}\!$	J-STD-003B



**Tape & Reel Packaging Dimensions:** 



Quantity per reel: 1.5K pcs