

3M™ Circuit Plating Tape 1280

Product Description

3M™ Circuit Plating Tape 1280 is a polyester film tape with unique adhesive for printed circuit board masking during electroplating.

Product Construction

Backing	Adhesive	Color	Standard Roll Length
Polyester	Silicone/Rubber blend	Red	72 yds. (65 m) 144 yds. (132 m)

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:	31 oz./in. width (33.9 N/100 mm)	D-3330
Tensile Strength at Break:	30 lbs./in. width (525.4 N/100 mm)	D-3759
Elongation at Break:	135%	D-3759
Backing Thickness:	0.9 mils (0.020 mm)	D-3652
Total Tape Thickness:	3.6 mils (0.091 mm)	D-3652

Features

- Low stretch polyester film for machine, as well as hand application.
- Solvent clean up of the board is recommended to facilitate subsequent soldering.
- Polyester backing reduces stretch and recovery of tape and associated uneven stop-off line.
- Thick adhesive coating reduces undercutting because adhesive helps block out solutions between fingers.

Application Ideas

- Masking of many printed wiring boards during solder stripping and precious metal plating of fingers.
- Splicing of silicone treated papers.

Application Techniques

- Must be firmly pressed down by equipment with rubber-covered rollers. Hand rolling usually does not provide enough pressure. A vivid outline of the circuit leads usually indicates that adequate pressure was used.
- Tape generally performs better when no ovens are used to heat tape and boards.



3M™ Circuit Plating Tape 1280

Storage

Store under normal conditions of 60° to 80°F (15° to 27°C) and 50% R.H. in the original carton.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

Certification/Recognition

MSDS: 3M has not prepared a MSDS for this product which is not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements.

RoHs Complaint/REACH Compliant: This product complies with the European Union's "Restriction of Hazardous Substances" (RoHs) initiative and with European REACH regulations 2002/95/EC and 2005/618/EC.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-251-8634. Address correspondence to: 3M, Electronics Markets Materials Division, 3M Center, Building 225-3S-06, St. Paul, MN 55144-1000. Our fax number is 651-778-4244 or 1-877-369-2923. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Markets Materials Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle. Printed in U.S.A.
©3M 2011. All rights reserved.
60-5002-0420-5



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)

[7010045149](#) [7010048795](#) [7010048800](#) [7010048801](#) [7010048802](#) [7010048803](#) [7010048804](#) [7010048805](#)
[7100093149](#) [1280-12x72](#)