

3M™ ROUND CONDUCTOR FLAT CABLE, 3770 SERIES
.050" 26 AWG STRANDED, TPE

ORDERING INFORMATION
3770/XX XX

NUMBER OF CONDUCTORS
(SEE TABLE)


NOTE:
CONTACT 3M FOR AVAILABILITY OF ADDITIONAL CONDUCTOR
COUNTS AND/OR CUSTOM ROLL LENGTHS.

TABLE 1			
NUMBER OF CONDUCTORS	3M PART NUMBER	DIMENSION A	DIMENSION B
09	3770/09	0.450±.010 [11.43]	0.400±.007 [10.16]
10	3770/10	0.500±.010 [12.70]	0.450±.007 [11.43]
14	3770/14	0.700±.010 [17.78]	0.650±.007 [16.51]
15	3770/15	0.750±.010 [19.05]	0.700±.007 [17.78]
16	3770/16	0.800±.015 [20.32]	0.750±.011 [19.05]
20	3770/20	1.000±.015 [25.40]	0.950±.011 [24.13]
24	3770/24	1.200±.015 [30.48]	1.150±.011 [29.21]
25	3770/25	1.250±.015 [31.75]	1.200±.011 [30.48]
26	3770/26	1.300±.015 [33.02]	1.250±.011 [31.75]
30	3770/30	1.500±.020 [38.10]	1.450±.015 [36.83]
34	3770/34	1.700±.020 [43.18]	1.650±.015 [41.91]
36	3770/36	1.800±.020 [45.72]	1.750±.015 [44.45]
37	3770/37	1.850±.020 [46.99]	1.800±.015 [45.72]
40	3770/40	2.000±.020 [50.80]	1.950±.015 [49.53]
50	3770/50	2.500±.020 [63.50]	2.450±.015 [62.23]
60	3770/60	3.000±.020 [76.20]	2.950±.015 [74.93]
64	3770/64	3.200±.020 [81.28]	3.150±.015 [80.01]



3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373



PHYSICAL :

INSULATION
MATERIAL: THERMOPLASTIC ELASTOMER, TPE (TPO TYPE)
COLOR: GRAY
MARKING
STANDARD: NONE

CONDUCTORS
MATERIAL: 26 AWG, 7 X 34 [7 X 0.160] TINNED STRANDED COPPER

ELECTRICAL :

VOLTAGE RATING: USA: 300V EU: <50V
INSULATION RESISTANCE: >1 X 10¹⁰Ω/10ft. [3m]

CHARACTERISTIC IMPEDANCE: UNBALANCED
104Ω
CAPACITANCE: 13.1 pF/ft [42.98 pF/m]
INDUCTANCE: 0.14 μH/ft [0.46 μH/m]
PROPAGATION DELAY: 1.36 ns/ft [4.46 ns/m]
VELOCITY OF PROPAGATION: 75%

NOTE: UNBALANCED IS MEASURED BETWEEN GROUND-SIGNAL-GROUND CONDUCTORS.

ENVIRONMENTAL :

TEMPERATURE RATING: -40°C TO +105°C
FLAMMABILITY RATING: USA: UL HORIZONTAL

- NOTES
- REGULATORY INFORMATION:
FOR REGULATORY INFORMATION
ABOUT THIS PRODUCT,VISIT
3m.com/regs OR CONTACT
YOUR 3M REPRESENTATIVE.

UL FILE NO: E42769,
STYLE NO: 20297
 - 26 AWG WIRE ON .050 INCH
CENTERS PERMITS MASS
TERMINATION TO A BROAD LINE OF
IDC CONNECTORS.
 - TPE INSULATION PROVIDES
EXCELLENT TRANSMISSION
PROPERTIES AT A LOW COST.
 - ZIPPABLE FOR BRANCHING OR
DISCRETE TERMINATION.
 - BLUE MARKING ON ONE EDGE OF
CABLE DESIGNATES WIRE #1.

INCH [MM]			
TOLERANCE - UNLESS NOTED			
	.X	.XX	.XXX
INCH	±.1	±.05	±.010
[] = DIM. FOR REFERENCE ONLY			

DIMENSIONS: INCH [MM]

DESIGN REFERENCE	NEXT ASSEMBLY	REV	ECO	ISSUE DATE AND DESCRIPTION	DRFT	CHKD
CODES		L	SCHMIDT	DEC 16,2021		
DIVISION	DIVISION CODE	CHKD	F RODRIGUEZ	JAN 04,2022	APPRVL	DATE
DO NOT SCALE DRAWING	SCALE 4 1	TOLERANCES EXCEPT AS NOTED				
THIRD ANGLE PROJECTION		INCHES .00 ± .000 ± .0000 ±				
		MILLIMETERS 0 ± .00 ± .000 ±				
MAX SURFACE ROUGHNESS 125 /	ALL SURFACES MARKED ONLY	ANGLES ±1 °				
TITLE ROUND CONDUCTOR FLAT CABLE SERIES 3770 .050" 26AWG STRANDED						
CAGE NUMBER	SIZE	DRAWING NO.	REV.			
D	78-5100-0342-5	F				
MODEL	DET	ISTS	YES	NO	SHT	1 OF 2

3M™ ROUND CONDUCTOR FLAT CABLE, 3770 SERIES
 .050" 26 AWG STRANDED, TPE

Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within User's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.


Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M Business Center
Electronics Materials Solutions Division
13011 McCallen Pass, BLDG C
Austin, TX 78753-5380
1-800-225-5373
www.3M.com/interconnect

3M ELECTRONICS MATERIALS SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3M.com/interconnect>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

DESIGN REFERENCE		NEXT ASSEMBLY		REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD	
ADDS CODES		 DESIGNS CODES 		DRFT L SCHMIDT		DATE DEC 16, 2022		MFG		DATE			
DIVISION		DIVISION CODE		ENGR F RODRIGUEZ		DATE JAN 04, 2022		APPVL		DATE			
DO NOT SCALE DRAWING		SCALE 4 1		TOLERANCES EXCEPT AS NOTED		3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2022 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or copied other than for 3M authorized purposes. All rights reserved.					
		INCHES .0 + .00 - .00 + .0000		MILLIMETERS 0 + 0 - .00 + .0000		TITLE ROUND CONDUCTOR FLAT CABLE SERIES 3770 .050" 26AWG STRANDED							
THIRD ANGLE PROJECTION						CASE NUMBER D		SIZE DRAWING NO. 78-5100-0342-5		REV. F			
MAX SURFACE ROUGHNESS 125		<input type="checkbox"/> ALL SURFACES <input checked="" type="checkbox"/> MARKED ONLY		ANGLES ± 1°		MODEL		DET. <input type="checkbox"/> YES <input checked="" type="checkbox"/> NO		SHT 2 OF			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[3770/15](#) [3770/60](#) [7100161736](#)