

GoggleGear™ 2890 Series

Description

The GoggleGear™ 2890 Series Safety goggles feature a modern design, Scotchgard™ Anti-fog lens coating, and are available either as non-vented or with indirect ventilation. They are suitable for a number of different applications where a comfortable goggle is required.

Key Features

- Absorbs 99.9 % UVA and UVB
- Cloth strap
- Wraparound lens



Product Number	3M I.D. Number	UPC	Description
GG2891-SGAF	70-0717-2991-0	00051131274372	3M™ GoggleGear™ GG2891-SGAF, Indirect vent, Clear Scotchgard™ Anti-fog lens 10ea/cs
GG2891S-SGAF	70-0716-9691-1	00051131274389	3M™ GoggleGear™ GG2891-SGAF, Sealed, vent, Clear Scotchgard™ Anti-fog lens 10ea/cs




Approximate Weight	
Eyewear	99g (3.5oz)
Approximate Physical Dimension	
Lens (Top)	170 mm
Lens (Height)	86 mm
Material Composition	
Lens	Polycarbonate (clear)
Shroud	PVC
Strap (clips)	Nylon
Strap (cloth)	PET
Strap (loop)	Polycarbonate

Regulatory/Standards (Markings)

- ANSI Z87.1-2015 (3M Z87+ U6 D3 D4) - Indirectly Vented Version
- ANSI Z87.1-2015 (3M Z87+ U6 D3 D4 D5) - Sealed Version
- CSA Z94.3 (Z94.3)

Representative Transmittance Spectrum (200 - 2000 nm)



ANSI Z87.1 Transmittance Requirement Classification	
Visible Light Filter (380 - 780 nm)	Clear
Ultraviolet Filter (200 - 380 nm)	U6
Infrared Filter (780 - 2000 nm)	Not rated
Welding Filter	Not rated

Other Noted Ratings

- Impact: Z87+
- Splash: D3
- Dust: D4
- Fine Dust: D5 (non-vented only)

Storage

Eyewear should be stored between temperatures of 50 °F (10 °C) and 86 °F (30 °C), in dry conditions with no chemical exposure, out of any direct exposure to radiation (sunlight, IR, UV, etc.), and in non-abrasive environments.

Cleaning

Thoroughly clean all surfaces with a mild soap solution and lukewarm water, then rinse. Dry with a soft cloth or tissue. Do not use any solvents on these lenses.

Product Number	3M I.D. Number	UPC	Description
GG2892-SGAF	70-0716-9692-9	00051131274396	3M™ GoggleGear™ GG2892-SGAF, Indirect Vent, Grey Scotchgard™ Anti-fog lens




Approximate Weight	
Eyewear	99g (3.5oz)
Approximate Physical Dimension	
Lens (Top)	170 mm
Lens (Height)	86 mm
Material Composition	
Lens	Polycarbonate (gray)
Shroud	PVC
Strap (clips)	Nylon
Strap (cloth)	PET
Strap (loop)	Polycarbonate

Regulatory/Standards (Markings)

- ANSI Z87.1-2015 (3M Z87+ U6 D3 D4) - Indirectly Vented Version
- CSA Z94.3 (Z94.3)

Representative Transmittance Spectrum (200 - 2000 nm)



ANSI Z87.1 Transmittance Requirement Classification	
Visible Light Filter (380 - 780 nm)	L3
Ultraviolet Filter (200 - 380 nm)	U6
Infrared Filter (780 - 2000 nm)	Not rated
Welding Filter	Not rated

Other Noted Ratings

- Impact: Z87+
- Splash: D3
- Dust: D4

Storage

Eyewear should be stored between temperatures of 50 °F (10 °C) and 86 °F (30 °C), in dry conditions with no chemical exposure, out of any direct exposure to radiation (sunlight, IR, UV, etc.), and in non-abrasive environments.

Cleaning

Thoroughly clean all surfaces with a mild soap solution and lukewarm water, then rinse. Dry with a soft cloth or tissue. Do not use any solvents on these lenses.

IMPORTANT NOTE

Before use, the wearer must read and understand the User Instructions provided as part of the product packaging.

Personal Safety Division

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

3M PSD products are
occupational use only.

In United States of America

Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/workersafety

In Canada

Technical Service: 1-800-267-4414
Customer Service: 1-800-364-3577
3M.ca/Safety

© 3M 2019. All rights reserved.
3M and GoggleGear are trademarks of 3M
Company and its affiliates.
Used under license in Canada.
All other trademarks are property
of their respective owners.
Please recycle.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7010302104](#) [7010386491](#) [7010386529](#)