

3M™ Very Low Outgassing High Shear Polyester Tape 8439FL

Product Description

3M™ Very Low Outgassing High Shear Polyester Tape 8439FL is a silver colored polyester film tape for the demanding requirements of hard disk drive and related electronics manufacturing. The metalized polyester backing offers low static and diffusivity and is complimented with a very low outgassing acrylic adhesive. This product offers a high level of permanence, yet is cleanly removable from most substrates even after extended heat treatments. This product uses 3M™ Non-Silicone Release Liner 5932.

Product Construction

Product	Backing	Adhesive	Liner	Color
3M™ Very Low Outgassing High Shear Polyester Tape 8439FL	Metalized Polyester, 1 mil	Acrylic	3M™ Non-Silicone Release Liner 5932	Silver

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

			ASTM Test Method
Adhesion to Stainless Steel:			D-3330
Initial	29 oz./in.		
After 30 hrs. @ 72°F	44 oz./in.		
After 30 hrs. @ 120°F	54 oz./in.		
After 30 hrs. @ 150°F	68 oz./in.		
Adhesion to Aluminum:			D-3330
Initial	22 oz./in.		
After 30 hrs. @ 72°F	41 oz./in.		
After 30 hrs. @ 120°F	48 oz./in.		
After 30 hrs. @ 150°F	69 oz./in.		
Shear Strength:			D-3654
0.5 in. x 0.5 in. w / 1750 gm load	> 10,000 min.		
0.5 in. x 0.5 in. w / 1000 gm load	> 10,000 min.		
Mechanical Performance:			D-3659
Tensile Strength	29 lb./in.		
Elongation @ Break	120%.		
Yield Point (%)	10%		
Yield Point (lbs./in.)	16 lbs./in.		



3M™ Very Low Outgassing High Shear Polyester Tape 8439FL

Typical Physical Properties and Performance Characteristics (continued)

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

ASTM Test Method		
Caliper:		D-3652
Backing	1.0 mil	
Adhesive	1.0 mil	
Total	2.0 mil	
Moisture Vapor Transmission Rate:	0.29 gms H ₂ O/24 hr/100 in ²	D-3833
Static¹:	< 100 volts	
NASA Outgassing:		E-595
Total Mass Loss (TML)	0.46%	
Condensable Materials (CVCN)	< 0.01%	
Water Vapor Recovered (WVR)	0.24%	
Outgassing by Headspace GC Analysis² (units = µg/cm²)		D-4526 ³
Hydrocarbons	< .05 µg/cm ²	
Acrylates	< .05 µg/cm ²	
Organic Acids	< .02 µg/cm ²	
Alcohols & Esters	< .05 µg/cm ²	
Siloxanes	< .02 µg/cm ²	
Anions by Ion Chromatography (units = ng/cm²)		
Fluoride	not detected	
Chloride	< 20 ng/cm ²	
Nitrite	not detected	
Bromide	not detected	
Nitrate	not detected	
Phosphate	not detected	
Sulfate	not detected	

¹ Static = Residual voltage on surface of tape after unwind @ 12 in./min. as measured by 3M Model 709 static sensor.

² Outgassing = Dynamic headspace analysis of volatile components collected during a 4 hr @ 80°C heat cycle using a Hewlett-Packard Model 5890 Series II gas chromatograph coupled with a Hewlett-Packard Model 5989B mass spectrometer.

³ ASTM test method modified per footnote #2 above.

Application Ideas

- Perimeter sealing of hard disk drive clamshells.
- Temporary porthole sealing of hard disk drive clamshells.
- Process aid.
- General purpose sealing.
- Other applications which require a low outgassing polyester film tape.

3M™ Very Low Outgassing High Shear Polyester Tape 8439FL

Key Attributes

Features	Advantages	Benefits
1 mil metalized polyester backing	Thin, high strength	Helps reduce breakage
	Bleeds static charge rapidly	Helps reduce risk of product damage due to electrostatic discharge
	Low diffusivity	Effective contamination barrier
	Low water vapor transmission rate	Effective barrier for water vapor
High purity acrylic adhesive	Low outgassing	Helps reduce risk of chemical contamination
	Low extractable ionic content	Helps reduce risk of chemical contamination
	Acrylic acid-free adhesive formulation	Helps reduce risk of chemical contamination
	Clean removability from a wide variety of substrate materials	Eliminate cleanup of substrate materials during rework operations
	Excellent shear strength	Helps reduce chance of tape slippage when shear stress is applied
	Long aging	Adhesive stable over long periods of time

General Information

- Best results obtained using firm rubdown pressure on clean, oil-free substrate materials.
- Dimensionally stable over temperature range from -60°F to 300°F (-51°C to 149°C).
- Standard packaging includes plastic cores and individual plastic bags.
- Shear performance decreases with increasing temperature.

Shelf Life

18 months from manufacture of material if properly stored at 60-80°F (16-27°C) and 40-50% relative humidity.

3M™ Very Low Outgassing High Shear Polyester Tape 8439FL

Certification/Recognition

MSDS: 3M has not prepared a MSDS for these products which are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, these products should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards.

TSCA: These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements.

RoHs Complaint/REACH Compliant: 3M™ Very Low Outgassing High Shear Polyester Tape 8439FL complies with the European Union's "Restriction of Hazardous Substances" (RoHs) initiative and with European REACH regulations 2002/95/EC and 2005/618/EC.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-251-8634. Address correspondence to: 3M, Electronics Markets Materials Division, 3M Center, Building 225-3S-06, St. Paul, MN 55144-1000. Our fax number is 651-778-4244 or 1-877-369-2923. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Markets Materials Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle. Printed in U.S.A.
©3M 2010. All rights reserved.
70-0707-3954-8



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)
[8439FL](#)