

June, 2017

3M™ Riveters Tape 685

Product Description

3M™ Riveters Tape 685 is a zone-coated polyester film tape with a tack-free center “window” for use in holding rivets in place both prior to and during riveting.

Product Features

- During riveting, helps ensure easy visibility of rivets and no adhesive transfer to rivet heads.
- Tough polyester film that resists shattering or slivering to help save time and increase output.
- Uncoated center “window” so it does not adhere to rivets in order to eliminate potential of adhesive transfer to rivet heads.
- Rubber adhesive for good immediate adhesion that resists stretching induced by bucking bar that might lead to film entrapment under rivet head for ease of application and to help reduce rework.



3M™ Riveters Tape 685

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Property	Values		Method
Color	Green adhesive, transparent film in uncoated center section		
Total Tape Thickness	0.043 mm	1.7 mil	ASTM D3652
Backing Thickness	0.025 mm	1 mil	ASTM D3652
Backing	Polyester film		
Adhesive	Rubber-strip coated along edges of tape only		

Typical Performance Characteristics

Property	Values		Method	Substrate
Peel Adhesion	3.3 N/cm	30 oz/in	ASTM D3330	Stainless Steel
Tensile Strength	33.3 N/cm	304 oz/in	ASTM D3759	

Available Sizes

Property	Values	
Standard Roll Length	32.9 m	36 yd

3M™ Riveters Tape 685

Available Sizes (continued)

Width

3/4 yd (19 mm) with 3/16 yd (4.8 mm) adhesive strip on each edge

1 yd (.25 mm) with 1/4 yd (6.4 mm) adhesive strip on each edge

Storage and Shelf Life

Store in a clean dry place at 60-80°F (15-27°C) and 40-50% relative humidity.

Shelf Life: No longer than 18 months from date of manufacture.

3M™ Riveters Tape 685

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

References

Safety Data Sheet (SDS)

https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&msdsLocale=en_US&co=ptn&q=685

3M™ Riveters Tape 685

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



Industrial Adhesives and Tapes
Division
3M Center
St. Paul, MN 55144-1000
800-362-3550
www.3M.com

Please recycle.
© 3M 2019. All Rights
Reserved.

The brands listed above are trademarks of
3M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)
[685](#)