




# Scotchlok™ Terminals

MU18-250DM, MU14-250DM, MU10-250DM

Male Disconnect, Non-Insulated, Butted Seam



## Data Sheet

Product Number	Wire Range (AWG)	Male Tab Width (W') x Thickness	L	Barrel Length	Barrel I.D.
MU18-250DM	22-18	0.250 x 0.032	0.73	0.25	0.065
MU14-250DM	16-14	0.250 x 0.032	0.73	0.25	0.085
MU10-250DM	12-10	0.250 x 0.032	0.75	0.25	0.150



UNDERWRITERS  
LABORATORIES  
STANDARD NO. UL 310  
3M FILE NO. E70512



CANADIAN STANDARDS  
ASSOCIATION  
STANDARD NO. C22.2  
NO. 153  
3M FILE NO. LR22190

## Installation Information

### ⚠ WARNING

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

UL Listed and CSA Certified for use on stranded copper (AWG) wire only.

Strip away the end 3/8 inch of wire insulation.

Make the crimp in the proper station of a recommended 3M crimp tool: TH-440, TH-450 (scissor style), or TR-490 (ratchet style) hand tools.



Barrel Crimp (Required)

## Specifications

Wire Size:  
Barrel Seam:  
Maximum Voltage Rating:

See Table Above  
Butted  
600 V Building Wire  
1000 V Signs or  
Fixtures (Luminaires)  
Same as Wire  
ETP Copper  
Tin

Maximum Current:  
Terminal Material:  
Plating:

Suitable for factory application on steel or brass tabs UL or CSA.

Suitable for field application on brass tabs, strain relief required, UL only.

## Engineering Specification

Crimp-Type Male Quick Disconnect shall, electrically and mechanically connect permanently to a prestripped end of a stranded copper wire and, have a flat rectangular tongue portion for mating to a Female Quick Disconnect in a separable, reusable manner, forming a Quick Connect Wiring Connection.

The connector line shall offer tongue variations (size 0.250 x 0.032 or 0.187 x 0.020 per ANSI/NEMA DC-2) and barrel variations in wire size 22-18 AWG, 16-14 AWG, 12-10 AWG and construction of non-insulated, vinyl insulated, nylon fully insulated, etc.

The Quick Disconnect shall have regulatory agency coverage (UL Listing, CSA Certification). The tongue shall be marked with the wire range and the manufacturer's symbol.(↑)

The Male Quick Disconnect shall be tin plated 0.032" thick copper, with a 0.250" blade conforming to ANSI/NEMA DC-2 dimensions and a 0.25" long barrel and sized for a specified (AWG) wire range (22-18, 16-14, 12-10).

Connectors shall be UL Listed and CSA Certified for 600 volts maximum, building wire: 1000 volts maximum, signs and fixtures (luminaires).

Quick Disconnect connectors shall be suitable for field or factory wiring, with a UL Recognized strain relief required.

3M and Scotchlok are trademarks of 3M.



is a trademark of Underwriters Laboratories.



is a trademark of Canadian Standards Association.

### IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

**Warranty; Limited Remedy; Limited Liability.** This product will be free from defects in material and manufacture as of the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**



### Electrical Products Division

6801 River Place Blvd.  
Austin, TX 78726-9000  
<http://www.3M.com/elpd>

Litho in USA.  
© 3M 2002 78-8125-9877-5-A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[MU10-250DMK](#) [MU14-250DMK](#) [MU18-250DMK](#)