

# Technical Specification Sheet

## 3M™ VFlex™ Particulate Respirator, 9105, N95

### Key Features

- NIOSH approved N95 rating
- Adjustable nose clip
- V-shaped pleats
- Flat-fold style
- Stapled headbands

### Material Composition

- Straps – Polyisoprene
- Staples - Steel
- Nose Clip – Aluminum
- Filter – Polypropylene
- Coverweb – Polypropylene
- This respirator contains no components made from natural rubber latex
- Approximate weight of product: 0.40 oz.
- See the 3M Technical Bulletin - [Cellulose Certification - Filtering Facepiece Respirators](#) for information about which 3M respirators contain cellulose

### Country of Origin

Made in the USA with globally sourced materials

### Use For

- Use for solid particulates and liquid mists in concentrations not exceeding 10X PEL/OEL
- Always follow User Instructions and use in manners as indicated



### Do Not Use For

- DO NOT use for gases and vapors, oil aerosols, asbestos, arsenic, cadmium, lead, 4,4-methylene dianiline (MDA), or abrasive blasting
- DO NOT use for particulate concentrations exceeding 10X PEL/OEL
- DO NOT use in any manner not indicated in the User Instructions

### Approvals and Standards

- NIOSH approved N95 particulate respirator
- Meets NIOSH 42 CFR 84 N95 requirements for a minimum 95% filtration efficiency against solid and liquid aerosols that do not contain oil.
- NIOSH approval number: TC-84A-5231
- Assigned Protection Factor (APF 10) per US OSHA and Canada CSA

## Ordering Information

Description	UPC	ID #	Respirators/Box	Boxes/Case	Each/Case
Particulate Respirator VFlex, 9105	50051131173977	70-0715-6389-7	50	8	400

### Time Use Limitation

Replace the respirator when it becomes dirty, damaged, or difficult to breathe through.

### Shelf Life and Storage

- 5 years from the date of manufacture
- Use By date on box in MM/YYYY format
- Store respirators in the original packaging, away from contaminated areas, dust, sunlight, extreme temperatures, excessive moisture, and damaging chemicals
- Store in temperatures between -4°F (-20°C) and +86°F (+30°C) and not exceeding 80% RH

### WARNING!

This respirator helps reduce exposures to certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. Follow all local regulations. In the U.S., a written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134, including training, fit testing and medical evaluation. In Canada, CSA standard Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. **Misuse may result in sickness or death.** For correct use, consult supervisor and the User Instructions or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.



#### Personal Safety Division

3M Center, Building 0235-2W-70  
St. Paul, MN 55144-1000  
3M.com/workersafety

3M PSD products are occupational use only.

### Acceptable Fit Test Protocols

Fit Test Protocol*		Acceptable with this product?
Qualitative Protocols	Saccharin	<input checked="" type="checkbox"/>
	Bitrex™	<input checked="" type="checkbox"/>
	Irritant Smoke	<input type="checkbox"/>
	Isoamyl Acetate	<input type="checkbox"/>
Quantitative Protocols		<input checked="" type="checkbox"/>

\*Refer to OSHA 1910.134

#### For More Information

Technical Assistance 1-800-243-4630  
Hours of Operation: M-Th 8am - 6pm, Fri 8am - 4:30 pm CST  
© 3M 2018. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[3M:](#)  
[9105](#)