

3M™ Bumpon™ Protective Products


Molded Shapes - Colored and Clear Series

SJ5000 • SJ5300 • SJ5400 • SJ5500 • SJ5700 • SJ6100

Product Description

3M™ Bumpon™ Protective Products Molded Shapes - Colored and Clear Series are pressure-sensitive, adhesive-backed polyurethane products. They can be used as feet, stops, spacers, and protectors in many applications.

The urethane is a durable, resilient elastomer. The aggressive, high tack, pressure sensitive adhesive is protected with a release liner making application fast and easy.



Features

All 3M™ Bumpon™ Protective Products feature a plasticizer-free, urethane composition which exhibits:

- Excellent skid resistance
- Long aging resiliency – will not crack or harden
- Abrasion resistance
- Resistance to marring and staining

Application Ideas

Use almost anywhere slamming, scratching, nicking, scuffing, marring, sliding, vibration, or noise could be a problem for your product.

- **Feet** on the bottom of small appliances, desk top or handheld electronic devices, electronic cabinetry, telephones, keyboards, foot pedals, scales, clocks, speakers, dispensers, and computers.
- **Stops** for cabinet doors, lids, and drawers.
- **Spacers** for picture frames to provide alignment; for electronic and automotive applications as an aid in assembly.
- **Protectors** to prevent damage in shipping, and keep parts from direct contact with each other.



3M™ Bumpon™ Protective Products


Molded Shapes - Colored and Clear Series

SJ5000 • SJ5300 • SJ5400 • SJ5500 • SJ5700 • SJ6100

3M™ Bumpon™ Protective Products

Cylindrical Shapes (with flat tops)

Molded Shape Number



Product Number

Bumpon SJ5012, SJ5312*, SJ5412**

Colors

Black, Brown, White, Gray, Transparent*, True White**

Width inches (mm)


0.50 (12.7)

Height inches (mm)

0.14 (3.5)

Pad Format

7x8 (56)




Bumpon SJ5744, SJ5344*

Black, Transparent*

0.75 (19.1)

0.16 (4.1)

4x10 (40)



Bumpon SJ5076, SJ5376*

Black, Transparent*


0.315 (8.0)

0.110 (2.8)

8x7 (56)

Cylindrical Shapes (with concave tops)

Molded Shape Number



Product Number

Bumpon SJ5001

Colors

Black

Width inches (mm)


0.50 (12.7)

Height inches (mm)

0.14 (3.5)

Pad Format

5x8 (40)




Bumpon SJ5009, SJ5309*

White, Gray, Brown, Black Transparent*

0.88 (22.3)

0.40 (10.1)

3x8 (24)



Bumpon SJ5532

Gray, Black


1.88 (47.7)

0.66 (16.7)

Separate Parts

Hemispherical Shapes

Molded Shape Number



Product Number

Bumpon SJ5302*, SJ5402**

Colors

Transparent*, True White**

Width inches (mm)


0.312 (7.9)

Height inches (mm)

0.085 (2.2)

Pad Format

8x18 (144)




Bumpon SJ5003*

Black, Brown, Gray, Transparent*

0.44 (11.1)

0.20 (5.0)

8x7 (56)



Bumpon SJ5306*, SJ5406**


Transparent*, True White**

0.375 (9.5)

0.150 (3.8)

6x8 (48)

Molded Shape Number



Product Number

Bumpon SJ5017, SJ5317*

Colors

White, Gray, Black, Transparent*

Width inches (mm)


0.75 (19.0)

Height inches (mm)

0.38 (9.6)

Pad Format

4x10 (40)




Bumpon SJ5027, SJ5327*

White, Gray, Brown, Black, Transparent*

0.63 (16.0)

0.31 (7.9)

5x8 (40)



Bumpon SJ5382*

Transparent*

0.25 (6.4)

0.075 (1.9)

8x18 (144)

*Bumpon SJ5300 series identifies transparent products. **Bumpon SJ5400 series identifies true white products.

Note: All dimensions ± 0.02 inches or ± 0.5 mm measured without the adhesive liner.

Important: Some Bumpon molded shapes listed (or specific color versions) may require special minimum order quantities. Consult your local 3M representative or our website: www.3M.com/Bumpons.

3M™ Bumpon™ Protective Products


Molded Shapes - Colored and Clear Series

SJ5000 • SJ5300 • SJ5400 • SJ5500 • SJ5700 • SJ6100

3M™ Bumpon™ Protective Products

Tapered Square Shapes

Molded Shape Number



Product Number

Bumpon SJ5705, SJ6105

Colors

Black

Width inches (mm)


1.275 (32.4)

Height inches (mm)

0.250 (6.4)

Pad Format

3x3 (9)




Bumpon SJ5007, SJ5307*

Black, White, Transparent*

0.413 (10.4)

0.98 (2.5)

6x9 (54)



Bumpon SJ5008, SJ5308*


White, Gray, Black, Transparent*

0.50 (12.7)

0.12 (3.1)

8x10 (80)

Molded Shape Number



Product Number

Bumpon SJ5514

Colors

White, Gray, Black

Width inches (mm)


0.81 (20.6)

Height inches (mm)

0.52 (13.1)

Pad Format

4x1 (4)




Bumpon SJ5018, SJ5318*

White, Gray, Brown, Black, Transparent*

0.50 (12.7)

0.23 (5.8)

8x10 (80)



Bumpon SJ5023, SJ5323*

White, Gray, Brown, Black, Transparent*

0.81 (20.5)

0.30 (7.6)


4x9 (36)

*Bumpon SJ5300 series identifies transparent products.

Note: All dimensions ± 0.02 inches or ± 0.5 mm measured without the adhesive liner.

Top Hat and Continuous Strip Shapes

Molded Shape Number



Product Number

Bumpon SJ6115 - Top Hat

Colors

Black

Diameter of Brim, inches (mm)

0.625 (15.9)

Height of Brim, inches (mm)


0.093 (2.36)

Total Height, inches (mm)

0.187 (4.75)

Form

5x8 (40)



Bumpon SJ6125 - Top Hat


Black

0.625 (15.9)

0.093 (2.36)

0.250 (6.35)

5x8 (40)



Bumpon SJ5510 - Continuous Strip*

White, Gray, Black, Brown

Width, inches (mm): 0.50 (12.7)

Height, inches (mm): 0.15 (3.88)

50' rolls, 5 rolls per case

Note: Dimensions for Bumpon SJ6115 and Bumpon SJ6125 ± 0.005 inches (± 0.13 mm) for diameter ± 0.015 inches (± 0.38 mm) for height measured without adhesive liner. Bumpon Top Hat products were created as an optional, non-skid foot shape, to be used in a recess (see page 7). They provide high resistance to removal, knock-off or shearing, when used in conjunction with a recessed location.

*Continuous molded strip can be cut by the customer to a specific length. The surface has lines that appear every 9" on the strip.

Important: Some Bumpon molded shapes listed (or specific color versions) may require special minimum order quantities. Consult your local 3M representative or our website: www.3M.com/Bumpons.

Special Products

Custom Shape and Color

3M can match most colors and customize shapes to your specifications. 3M has over 100 available standard and custom molded shapes. Electronic format (CAD and PDF) drawings are available on request.

Special Easy Strip Packaging

Packaged into strips or die cut and perforated pads can help simplify some assembly operations. Product currently available:

- 3M™ Bumpon™ Protective Product SJ5518 die cut perforated on pads of 64
- 3M™ Bumpon™ Protective Product SJ5508 die cut and perforated on pads of 64
- 3M™ Bumpon™ Protective Product SJ5523 4x1 matrix separated by perforations
- 3M™ Bumpon™ Protective Product SJ5514 4x1 matrix separated by perforations

Note: Custom Bumpon products may require a qualifying minimum quantity and/or a one time set-up charge. Call your local 3M sales representative for more information.

3M™ Bumpon™ Protective Products

Molded Shapes - Colored and Clear Series

SJ5000 • SJ5300 • SJ5400 • SJ5500 • SJ5700 • SJ6100

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		3M™ Bumpon™ Protective Products		
	3M Test Method	SJ5000 SJ5500 SJ5700	SJ5300 SJ5400	SJ6100
Hardness, Shore M	ASTM-D2240	72	75	72
Resilience, %	ASTM-D2632, 0.125" sample	30	5	30
Kinetic Coefficient of Friction (Mk) (Dependent on Test Surface) ¹	ASTM-D1894			
	Stainless Steel	>1	>1	>1
	Glass	>1	>1	>1
	Formica® laminate	0.9-1.4	0.9-1.4	0.9-1.4
	Wood	0.9-1.4	0.9-1.4	0.9-1.4
Abrasion Resistance (Taber H18, 1kg) g/1000 cycles ²	ASTM-C501	1.7-1.9	0.13	1.7-1.9
Tensile, lbs/in ² (MPa) ²	ASTM-D412, Die A	600 (4.1)	740 (5.1)	600 (4.1)
Elongation,% ²	ASTM-D412, Die A	100	65	100
Dielectric Strength, volts/mil ²	ASTM-D1000	200	370	200
Stain Resistance ³	3M-24 hours @ 158°F against white paint 7 days exposed to UV.	No Staining	No Staining	No Staining
Flammability Listing	UL-94HB	Pass; UL Recognized	Not UL Recognized	Pass; UL Recognized
Application Temperature		40°F (5°C) to 125°F (52°C)		
Service Temperature	Constant: Intermittent:	-30°F (-34°C) to 150°F (66°C) Up to 225°F (107°C)		
Solvent and Fuel Resistance ³	24 hour immersion			
	5% Detergent in water	No Apparent Effect		
	25% Ammonia in water	No Apparent Effect		
	Bleach	No Apparent Effect		
	Hydrochloric Acid (1 Normal Solution)	No Apparent Effect		
	Diesel Fuel	No Apparent Effect		
	Auto Oil	No Apparent Effect		
	Isopropyl Alcohol	Slight Swelling		
	Heptane	Slight Swelling		
Toluol	Considerable Swelling			
Lacquer Thinner	Considerable Swelling			

Notes:

¹Two important laws of friction applicable to Bumpon products are: (1) Friction is independent of the area of contact between solids and (2) friction is proportional to the load between solid surfaces. Thus, if the load (weight) is doubled the force required to cause sliding is also double. This is expressed mathematically as follows: Sliding Force = M_k x weight.

²These properties were run on sheet material from the same materials as the individual Bumpon products

³Reference test for 24 hours. Results may vary for different product application conditions.

3M™ Bumpon™ Protective Products

Molded Shapes - Colored and Clear Series

SJ5000 • SJ5300 • SJ5400 • SJ5500 • SJ5700 • SJ6100

Relative Adhesive Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

3M™ Bumpon™ Protective Products			
	SJ5000 SJ5500 SJ5700	SJ5300 SJ5400	SJ6100
Adhesive:	Natural Rubber R-30	Acrylic A-20	Synthetic Rubber R-25
Initial Adhesion Low Surface Energy: High Surface Energy:	Good Good	Poor Fair	Excellent Excellent
Adhesion (Peel) Low Surface Energy: High Surface Energy:	Good Good	Poor Good	Excellent Excellent
Static Shear 75°F (25°C): 120°F (49°C): 158°F (70°C):	Excellent Good Poor	Excellent Excellent Excellent	Excellent Good Fair
Dynamic Shear:	Good	Excellent	Good
Solvent Resistance:	Good	Excellent	Good

Adhesive Performance

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

The following table on peel adhesion provide representative performance characteristics of the adhesive systems used in the construction of 3M™ Bumpon™ Protective Products molded series products.

90° Peel Adhesion

*Peel Force, oz. Per 1/2 inch

3M™ Bumpon™ Protective Products			
	SJ5000 SJ5500 SJ5700	SJ5300 SJ5400	SJ6100
Substrate:	Natural Rubber R-30	Acrylic A-20	Synthetic Rubber R-25
Polypropylene	25	3	52
Polystyrene	25	11	55
ABS	25	25	55
Stainless Steel	22	25	55
Aluminum	22	25	55

*3M Test Method TM-2011; 72 hour dwell, 1/2 inch wide samples pulled at 12 inches per minute. Testing completed using Bumpon Resilient Rollstock products SJ5816, SJ6016, and SJ6216, which use the same adhesive system as the molded series products.

3M™ Bumpon™ Protective Products

Molded Shapes - Colored and Clear Series


SJ5000 • SJ5300 • SJ5400 • SJ5500 • SJ5700 • SJ6100

Application Techniques

To obtain maximum adhesion, surfaces must be unified, dry, and free of contaminants. Surface contact is essential to adhesive performance. To maximize contact on a substrate:

- Clean surfaces with low strength solvent such as isopropyl alcohol (rubbing alcohol) or heptane.*
- Apply firm pressure to help increase the cold flow and contact of the adhesive with the substrate.
- Allow time (dwell) to increase the surface contact and adhesion (see illustrations below).

***Note:** Be sure to follow the manufacturer's precautions and directions for use when using solvents.



Environmental Exposure

Colored and transparent 3M™ Bumpon™ Protective Products are intended for interior applications where resilience and other physical properties will remain unchanged. When exposed to UV light for extended periods some slight discoloration or yellowing may occur.

Bumpon products may be used outdoors in a protected area with some discoloration possible; colored Bumpon products may chalk.

Simultaneous exposure to high humidity and temperature may degrade (soften) the Bumpon product urethane.

3M™ Bumpon™ Protective Products

Molded Shapes - Colored and Clear Series

SJ5000 • SJ5300 • SJ5400 • SJ5500 • SJ5700 • SJ6100

Product Selections Considerations

Alignment

Alignment is more difficult with a rectangular shaped 3M™ Bumpon™ Protective Product when no recess is provided.

Circular shaped product



(top view)

Rectangular shaped product



(top view)

Point of Contact

The point of contact provides either a large contact area or a very small (point) contact area depending on the shape of the Bumpon product.

Flat



(side view)

- Increased load capacity
- Better wear resistance

Hemisphere



(side view)

- Increased sound dampening
- Increased energy absorption

Profile

The profile is defined by the height and the diameter (or width) of the Bumpon product.

Low Profile



- Increased load capacity
- Less susceptible to being sheared off substrate

High Profile



- Better heat dissipation
- Not recommended if sideways shearing is possible

Recess

A recess is not necessary; however, there are several benefits to providing a recess.



- Provides target area for the Bumpon product during attachment process
- Improves adhesion performance: impact absorption and shear strength
- Provides neater appearance
- Provides uniform location

Storage

Store in original cartons at 60° to 80°F (16° to 27°C) and 40 to 50% relative humidity.

Shelf Life

To obtain best performance, use this product within 18 months from date of manufacture.

3M™ Bumpon™ Protective Products

Molded Shapes - Colored and Clear Series

SJ5000 • SJ5300 • SJ5400 • SJ5500 • SJ5700 • SJ6100

Regulatory

For regulatory information about this product, refer to our website at 3M.com.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-251-8634. Address correspondence to: 3M, Electronics Markets Materials Division, 3M Center, Building 225-3S-06, St. Paul, MN 55144-1000. Our fax number is 651-778-4244 or 1-877-369-2923. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Markets Materials Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/Bumpons

3M and Bumpon are trademarks of 3M Company.
Formica is a registered trademark of the Formica Corporation.
Please recycle. Printed in U.S.A.
© 3M 2012. All rights reserved.
60-5002-0526-9



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[SJ-5008 \(BROWN\)](#) [SJ-5027 \(BROWN\)](#) [SJ-5009 \(BROWN\)](#) [SJ-5532 BROWN](#) [SJ-5518 \(WHITE\)](#) [SJ-5518 \(BROWN\)](#)
[SJ-5508 \(WHITE\)](#) [SJ-5532 WHITE](#) [SJ-5003 \(BROWN\)](#) [SJ-5508 \(BROWN\)](#) [SJ-5017 \(BROWN\)](#) [SJ-5023SP\(BLACK\)](#)
[SJ-5744 GRAY](#) [SJ5398](#)