

3M™ Water Filtration Products

SPEC# _____

QUANTITY _____

application: **MULTIPLE EQUIPMENT**

models:

High Flow Series Replacement Cartridges HF8-S thru HF35



3M™ Water Filtration Products line of replacement cartridges offer multiple solutions to help improve the taste, appearance and consistency of your product at flow rates from 0.75 gpm to 6 gpm.

PRODUCT BENEFITS

- Sanitary Quick Change (SQC) encapsulated cartridge design reduces media contamination during change-outs.
- Expansive breadth of product offering that can accommodate most applications.
- Multiple choice of medias to help provide solutions for varying water conditions.
- FDA CFR-21 compliant materials.
- NSF Certified; 3M Purification Inc: Commercial Modular-High Flow Series¹, Components-Commercial Modular², Components-Filter Cartridges³.

PRODUCT SPECIFICATIONS

Model No.	Part No	3M ID#	Micron Rating	Claims	Flow Rate	Capacity
HF35 ¹	5615205	70020043090	1	Particulate, Chlorine Taste & Odor	1.67 gpm (6.3 lpm)	12,600 gals. (47,696 lit.)
HF35-S ¹	5615207	70020114156	1	Particulate, Chlorine Taste & Odor, Scale Inhibitor**	1.67 gpm (6.3 lpm)	12,600 gals. (47,696 lit.)
HF35-MS ¹	5615211	70020043108	1	Particulate Class I, Chlorine Taste & Odor, Scale Inhibitor**	1.67 gpm (6.3 lpm)	12,600 gals. (47,696 lit.)
HF25 ¹	5615201	70020020619	1	Particulate Class I, Chlorine Taste & Odor	1.5 gpm (5.7 lpm)	10,000 gals. (37,854 lit.)
HF25-S ¹	5615203	70020020627	1	Particulate Class I, Chlorine Taste & Odor, Scale Inhibitor**	1.5 gpm (5.7 lpm)	10,000 gals. (37,854 lit.)
HF25-MS ¹	5615209	70020020635	1	Particulate Class I, Chlorine Taste & Odor, Scale Inhibitor**	1.5 gpm (5.7 lpm)	10,000 gals. (37,854 lit.)
HF25-S-SR ²	5615240	70020302298	5	Particulate**, Scale Inhibitor**, Fits Standard (A3) Keyed heads	2 gpm (7.6 lpm)	N/A
HF25-S-SR5 ²	5615238	70020302900	5	Particulate**, Scale Inhibitor**, Fits Black (A5) Keyed heads	2 gpm (7.6 lpm)	N/A
HF27*	5615227	70020154475	5	Particulate**, Chlorine Taste & Odor	1.5 gpm(5.7 lpm)	4800 gals. (18,170 lit.)
HF27-S*	5615231	70020201995	5	Particulate**, Chlorine Taste & Odor, Scale Inhibitor**	1.5 gpm(5.7 lpm)	4800 gals. (18,170 lit.)
HF05-MS ¹	5609327	70020044312	1	Particulate**, Chlorine Taste & Odor, Scale Inhibitor**	0.75 gpm (2.8 lpm)	1,500 gals. (5,678 lit.)
HF15-MS ¹	5609331	70020044320	5	Particulate**, Chlorine Taste & Odor, Scale Inhibitor**	1.0 gpm (3.8 lpm)	3,500 gals. (13,249 lit.)
HF8-S ³	5582106	70020016104	N/A	Scale Inhibitor**	6.0 gpm (22.7 lpm)	N/A

* Products not NSF certified

**As tested and verified by manufacturer's laboratory.



Replacement Cartridges

SPEC# _____
 QUANTITY _____
 MODEL NUMBER _____
 PART NUMBER _____

3M™ Water Filtration Products

SPECIFICATIONS

- Maximum operating pressure of 125 psi (862 kPa) and operating temperature of 100° (37.8°C).
- Materials are FDA CFR-21 Compliant.
- Shipping weight: Refer to Price Book
- Operating weight: Contact factory

IMPORTANT: INSTALLATION TIPS

These installation tips are for informational purposes only and are not intended to be used as actual installation instructions.

⚠ WARNING: To reduce the risk associated with the ingestion of contaminants:

- **Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.**

CAUTION: To reduce the risk associated with property damage due to water leakage:

- **Read and follow** Use Instructions before installation and use of this system.
- Installation and use **MUST** comply with all state and local plumbing codes.
- **Protect from freezing**, remove filter cartridge when temperatures are expected to drop below 40°F (4.4°C).
- **Do not install on hot water supply lines.** The maximum operating water temperature of this filter system is 100°F (37.8°C).
- **Do not install** if water pressure exceeds 125 psi (862 kPa). If your water pressure exceeds 80 psi (552 kPa), you must install a pressure limiting valve. Contact a plumbing professional if you are uncertain how to check your water pressure.
- **Do not install** where water hammer conditions may occur. If water hammer conditions exist you must install a water hammer arrester. Contact a plumbing professional if you are uncertain how to check for this condition.
- The disposable filter cartridge **MUST** be replaced every twelve (12) months, at the rated capacity or sooner if a noticeable reduction in flow rate occurs.

Model No.	Part No.	Shipping Dimension	Weight	Case Qty
HF35	5615205	10-1/2" x 10-1/2" x 28-1/4" (26.7 cm. x 26.7 cm. x 71.8 cm)	9 lbs.(4.1 kg.)	4
HF35-S	5615207	10-1/2" x 10-1/2" x 28-1/4" (26.7 cm. x 26.7 cm. x 71.8 cm)	9 lbs.(4.1 kg.)	4
HF35-MS	5615211	10-1/2" x 10-1/2" x 28-1/4" (26.7 cm. x 26.7 cm. x 71.8 cm)	9 lbs.(4.1 kg.)	4
HF25	5615201	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	10 lbs. (4.5 kg.)	6
HF25-S	5615203	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	10 lbs. (4.5 kg.)	6
HF25-MS	5615209	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	10 lbs. (4.5 kg.)	6
HF25-S-SR	5615240	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	10 lbs. (4.5 kg.)	6
HF25-S-SR5	5615238	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	10 lbs. (4.5 kg.)	6
HF27	5615227	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	25 lbs. (11.3 kg.)	6
HF27-S	5615231	15-1/4" x 10-1/2" x 23-1/4" (38.7 cm. x 26.7 cm. x 59.1 cm)	25 lbs. (11.3 kg.)	6
HF05-MS	5609327	20-3/8" x 10-1/2" x 15-3/4" (51.8 cm. x 26.7 cm. x 40.0 cm)	7.5 lbs. (3.4 kg.)	8
HF15-MS	5609331	20-3/8" x 10-1/2" x 15-3/4" (51.8 cm. x 26.7 cm. x 40.0 cm)	10 lbs. (2.3 kg.)	8
HF8-S	5582106	10-1/4" x 2-3/4" x 2-1/4" (26.0 cm. x 7.0 cm. x 5.7 cm)	11 lbs. (5 kg.)	10

LIMITED WARRANTY

3M Purification Inc. warrants this Product will be free from defects in material and manufacture for one (1) years from the date of purchase: This warranty does not cover failures resulting from abuse, misuse, alteration or damage not caused by 3M Purification Inc. or failure to follow installation and use instructions. No warranty is given as to the service life of any filter cartridge or membrane as it will vary with local water conditions and water consumption. **3M PURIFICATION INC. MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOMER OR USAGE OF TRADE.** If the Product fails to satisfy this Limited Warranty during the warranty period, 3M Purification Inc. will replace the Product or refund your Product purchase price. This warranty does not cover labor. **The remedy stated in this paragraph is Customer's sole remedy and 3M Purification Inc.'s exclusive obligation. For additional information, see the entire Limited Warranty located in the product Installation and Operating Instruction Manual.**

Limitation of Liability. 3M Purification Inc. will not be liable for any loss or damage arising from this 3M Purification Inc. product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. Some states and countries do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you.



3M Purification Inc.
 400 Research Parkway
 Meriden, CT 06450 U.S.A.
 Toll Free: 1-866-990-9785
 Worldwide: 203-237-5541
 Fax: 203-238-8701
 www.3Mfoodservice.com • 3Mpurification.com

3M is a trademark of 3M Company.
 © 2013 3M Company. All rights reserved.
 70020303122 REV 0513

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7000001676](#) [7000001677](#) [7000050414](#) [7100041863](#) [7100051029](#) [7100054812](#) [7100069906](#) [7100090355](#)