



Very Low Outgassing High Shear Polyester Tape

8439

Technical Data

October, 2005

Supersedes September, 1999

Product Description

A silver colored polyester film tape for the demanding requirements of hard disk drive and related electronics manufacturing. The metalized polyester backing offers low static and diffusivity and is complimented with a very low outgassing acrylic adhesive. This product offers a high level of permanence, yet is cleanly removable from most substrates even after extended heat treatments.

Construction

Backing	Adhesive	Color
Metalized Polyester, 1 mil	Acrylic	Silver

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Adhesion to Steel:		D-3330
Initial	29 oz./in.	
After 30 hrs @ 72°F	44 oz./in.	
After 30 hrs @ 120°F	54 oz./in.	
After 30 hrs @ 150°F	68 oz./in.	
Adhesion to Aluminum:		D-3330
Initial	22 oz./in.	
After 30 hrs @ 72°F	41 oz./in.	
After 30 hrs @ 120°F	48 oz./in.	
After 30 hrs @ 150°F	68 oz./in.	
Shear Strength:		D-3654
0.5 in. x 0.5 in. w/1750 gm load	> 10,000 min.	
0.5 in. x 0.5 in. w/1000 gm load	> 10,000 min.	
Mechanical Performance:		D-3659
Tensile Strength	29 lb./in.	
Elongation @ Break	120%	
Yield Point (%)	10%	
Yield Point (lbs./in.)	16 lb./in.	
Caliper:		D-3652
Backing	1.0 mil	
Adhesive	1.0 mil	
Total	2.0 mil	
Moisture Vapor Transmission Rate:	0.29 gms H ₂ O/24 hr/100 in ²	D-3833
Static ¹ :	< 100 volts	
NASA Outgassing:		E-595
Total Mass Loss (TML)	0.46%	
Condensable Materials (CVCM)	< 0.01%	
Water Vapor Recovered (WVR)	0.24%	

3M™ Very Low Outgassing High Shear Polyester Tape

8439

Typical Physical Properties and Performance Characteristics (continued)

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

		ASTM Test Method
Outgassing by Headspace CG Analysis ² (units = µg/cm ²)		D-4526 ³
Hydrocarbons	< .05 µg/cm ²	
Acrylates	< .05 µg/cm ²	
Organic Acids	< .02 µg/cm ²	
Alcohols & Esters	< .05 µg/cm ²	
Siloxanes	< .02 µg/cm ²	
Anions by Ion Chromatography (units = ng/cm ²)		
Fluoride	not detected	
Chloride	< 20 ng/cm ²	
Nitrite	not detected	
Bromide	not detected	
Nitrate	not detected	
Phosphate	not detected	
Sulfate	not detected	

¹ Static = Residual voltage on surface of tape after unwind @ 12 in./min. as measured by 3M Model 709 static sensor.

² Outgassing = Dynamic headspace analysis of volatile components collected during a 4 hr @ 80°C heat cycle using a Hewlett-Packard Model 5890 Series II gas chromatograph coupled with a Hewlett-Packard Model 5989B mass spectrometer.

³ ASTM test method modified per footnote #2 above.

Application Ideas

- Perimeter sealing of hard disk drive clamshells.
- Temporary porthole sealing of hard disk drive clamshells.
- Process aid.
- General purpose sealing.
- Other applications which require a low outgassing polyester film tape.

Key Attributes

Features	Advantages	Benefits
<ul style="list-style-type: none"> • 1 mil metalized polyester backing 	<ul style="list-style-type: none"> • Thin, high strength • Bleeds static charge rapidly 	<ul style="list-style-type: none"> • Helps reduce breakage • Helps reduce risk of product damage due to electrostatic discharge
	<ul style="list-style-type: none"> • Low diffusivity • Low water vapor transmission rate 	<ul style="list-style-type: none"> • Effective contamination barrier • Effective barrier for water vapor
<ul style="list-style-type: none"> • High purity acrylic adhesive 	<ul style="list-style-type: none"> • Low outgassing 	<ul style="list-style-type: none"> • Helps reduce risk of chemical contamination
	<ul style="list-style-type: none"> • Low extractable ionic content 	<ul style="list-style-type: none"> • Helps reduce risk of chemical contamination
	<ul style="list-style-type: none"> • Clean removability from a wide variety of substrate materials 	<ul style="list-style-type: none"> • Eliminate cleanup of substrate materials during rework operations
	<ul style="list-style-type: none"> • Excellent shear strength 	<ul style="list-style-type: none"> • Helps reduce chance of tape slippage when shear stress is applied
	<ul style="list-style-type: none"> • Long aging 	<ul style="list-style-type: none"> • Adhesive stable over long periods of time

3M™ Very Low Outgassing High Shear Polyester Tape

8439

General Information

- Best results obtained using firm rubdown pressure on clean, oil-free substrate materials.
- Dimensionally stable over temperature range from -60°F to 300°F (-51°C to 149°C).
- Standard packaging includes plastic cores and individual plastic bags.
- Shear performance decreases with increasing temperature.

Shelf Life

18 months from manufacture of material if properly stored at 60-80°F (16-27°C) and 40-50% relative humidity.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-251-8634. Address correspondence to: 3M Electronics Markets Materials Division, Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55144-1000. Our fax number is 651-778-4244 or 1-877-369-2923. In Canada, phone: 1-800-634-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Product Use

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.

Warranty and Limited Remedy

Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.

Limitation of Liability

Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



3M Electronics

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics



Recycled Paper
40% pre-consumer
10% post-consumer

Printed in U.S.A.
©3M 2005 70-0707-3954-8 (10/05)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7010416859](#) [7100167027](#) [7100167028](#)