

Scotch® Vinyl Electrical Tape 35

Data Sheet

November 2020

Product Description

Scotch® Vinyl Electrical Tape 35 is a 7-mil thick, premium grade color-coding all-weather vinyl insulating tape. It is designed to perform in ambient temperatures up to 221°F (105°C). The tape is conformable for cold weather application down to 14°F (-10°C). It has excellent resistance to abrasion, moisture, alkalies, acids, corrosion and varying weather conditions (including UV exposure). The combination of an elastic PVC backing and aggressive pressure-sensitive rubber-based adhesive provides moisture-tight electrical and mechanical protection.

- For residential, commercial and industrial environments.
- More permanent phase identification, color coding of motor lead and piping systems.
- Long-lasting, fade-resistant marking for safety areas and equipment.
- Easily identified insulation for electrical wiring.
- Marking and identifying cable on cell sites.
- Suitable for harsh indoor and weather protected outdoor uses.
- Available in 10 fade-resistant colors, listed below.

Typical Properties

Physical Properties	Typical Value ^{3,4} Imperial (Metric)	Electrical Property	Typical Value ^{3,4} Imperial (Metric)
Temperature Rating - UL 510 ¹	176°F (80°C)	Voltage Rating UL 510 ¹ CSA ²	600 V 1000 V
CSA - C22.2 No. 197 ²	14°F (-10°C) 221°F (105°C)	Dielectric Strength ⁴ Standard Condition V/mil High Humidity	1250 V/mil (49.2 kV/mm) 90% of std.
Colors ⁵	Blue, Brown, Gray, Green, Orange, Pink, Red, Violet, White, Yellow	Insulation Resistance ⁴ (High Humidity Method)	>1x10 ⁶ megohms
Thickness ⁴	7 mils (0.178 mm)		
Adhesion to Steel ⁴	20 oz/in (2.2 N/cm)		
Adhesion to Backing ⁴	20 oz/in (2.2 N/cm)		
Breaking Strength ⁴	17 lb/in (30 N/cm)		
Elongation ⁴	225%		
Flame Retardant - UL 510	Pass		

Notes:

1. In accordance with the National Electrical Code, NFPA 70
2. In accordance with Canadian Electrical Code, Part 1
3. Not for specification. Values are typical, not to be considered minimum or maximum.
4. ASTM D1000 Test Method - properties measured at room temperature 73°F (23°C) unless otherwise stated
5. Color White is rated as UL Sunlight Resistant

Agency Approvals & Self Certifications

- UL Listed: UL 510 Standard "Insulating Tape", Category OANZ, File No. E129200
- CSA Listed: CSA-C22.2 No.197 "PVC Insulating Tape", File No. 048769, Class 9052-02
- VDE Marks License no. 130462 for Type 6: IEC 60454-3-1-6/F-PVCP/90
- Self-certified to meet Commercial Item Description: A-A-55809, Code A
- For Regulatory information including RoHS, REACH, please visit www.3M.com/regs



Scotch® Vinyl Electrical Tape 35

Installation Techniques	Scotch® Vinyl Electrical Tape 35 shall be applied in half-lapped layers with sufficient tension to produce a uniform wind (for most applications this tension will reduce the tape width to approximately 5/8 of original width). On pigtail splices, the tape shall be wrapped beyond the end of the wires and then folded back, leaving a protective cushion to resist cut-through. Wrap tape up-hill, taping from a smaller diameter surface to a larger diameter surface. Apply the tape with no tension on the last wrap to prevent flagging.
Shelf Life & Storage	This product has a 5-year shelf life (from date of manufacture) when stored in humidity-controlled storage (50°F/10°C to 80°F/27°C and <75% relative humidity).
Availability	Scotch® Vinyl Electrical Tape 35 is available from 3M authorized distributors Also available from 3M.com/electrical or call 1.800.245.3573.

3M, Scotch® and are trademarks of 3M Company.

Important Notice	All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.
Warranty; Limited Remedy; Limited Liability	This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Electrical Markets Division

Austin, TX

Phone: 800-245-3573

www.3M.com/electrical

Please Recycle. Printed in USA.

© 3M 2020. All Rights Reserved.

78-8124-4858-3 Rev H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[7010411602](#)