

3M Chip Carrier Sockets 8400 Series

Product Specification 78-5102-0186-2

Revised 5-7-13

Table of Contents

	Title Page	1
	Contents	2
1.0	Scope	3
2.0	3M Customer Documents	3
3.0	Performance Testing	3
4.0	Performance and Characteristics Overview	3
5.0	Electrical	4
6.0	Mechanical	4
7.0	Environmental	4
	Disclaimer	5
	Important Notice	5
	Warranty Information	5

Steven A. Neu: Approved 05-15-13
Jim W. Wessman: Approved 05-15-13



1.0 Scope

This document summarizes test methods, test conditions, and product performance requirements for the 3M Chip Carrier Sockets 8400 Series. In the event of performance data conflicts between this specification and any documents listed below, this specification supersedes those documents. Materials and finishes listed in the documents below apply and are included in this specification for reference only.

2.0 3M Customer Documents

78-5100-2147 Technical data sheet for 3M Chip Carrier Sockets, Surface Moun

78-5100-2148 Technical data sheet for 3M Chip Carrier Sockets, Low Profile, 4-Row, Through-Hole 8400 Series

3.0 Performance Testing

Unless otherwise specified, all tests shall be performed on 84XX-X1B1-RK-TP sockets at ambient environmental conditions. Unless otherwise specified, all values and limits are typical of those obtained by qualification testing of the subject product. All specifications are subject to revision and change without notice from 3M.

4.0 Performance and Characteristics Overview

4.1 Ratings

Dielectric Withstanding Voltage: 1000 V_{AC} for 1 minute

Temperature: -40°C to +105°C

Insulation resistance: >10 x10⁹ Ω at 500 V_{DC}

4.2 Materials

Through-Hole Socket:

Housing insulation: Glass filled PBT, black, 94V-0
Contact: Copper alloy

Surface Mount Socket:

Insulation: Glass filled PPS, black, 94V-0
Contact: Copper alloy

4.3 Finishes

Plating:

Nickel: Underplating: 50 μ" [1.27 μm] Nickel - Overall (Minimum)

Solder Tails: 100 μ" [2.54 μm] Matte Tin (Minimum)

Wiping Area: 100 μ" [2.54 μm] Matte Tin (Minimum)

4.4 Regulatory Compliance

See Regulatory Information Appendix (RIA) in the "RoHS compliance" section of www.3Mconnectors.com for compliance information. See customer drawings for regulatory specifics on each connector.

5.0 Electrical

Description or Parameter	Values & Limits	Units	Requirement or Conditions	Test Standard or Method
Dielectric Strength	500	Volts _{AC}	Measured between adjacent and opposing contacts. No disruptive discharge during 1 minute duration.	-
Contact interface resistance	30	Milliohms (Initial)	30 milliohm maximum ΔR contact resistance per interface throughout testing.	-
Insulation resistance	>10000	Megohms	Measured between contacts and insulator with 500 V _{DC} .	-
Capacitance	<1.0	pF	Less than 1.0 pF capacitance at 1000 kHz	-

6.0 Mechanical

Description or Parameter	Values & Limits	Units	Requirement or Conditions	Test Standard or Method
Vibration	10-2,000	Hz	Tested at 0.06 inch double amplitude per MIL-STD-1344A Method 2005.1	MIL-STD-1344A Method 2005.1
	20	G's		
Mechanical Shock	100	G's	Specimen subject to 100 G's half sine in 6 milisecs per MIL-STD-1344A Method 2004.1	MIL-STD-1344A Method 2004.1
Acceleration	15	G's	Per MIL-STD-810C Method 513.2	MIL-STD-810C Method 513.2
Contact Force	170	g / per pin	Through-hole socket	-
	210	g / per pin	Surface mount socket	
Durability	125	Cycles	Mating and unmating cycle rate not exceeding 10 cycles/minute per MIL-STD-1344 Method 2D16	MIL-STD-1344 Method 2D16

7.0 Environmental

Description or Parameter	Values & Limits	Units	Requirement or Conditions	Test Standard or Method
Thermal Shock	-55 to +105	°C	No physical abnormalities or damage. Per MIL-STD-1344, method 1003, condition A.	MIL-STD-1344 Method 1003
Humidity-Temperature Cycling	80	°C	Tested for 16 hours per MIL-STD-1344, method 1002	MIL-STD-1344 Method 1002
	85	% Rel. Humidity		

3M is a trademark of 3M Company.

Disclaimer

Unless otherwise noted, references to industry specifications are intended to indicate substantial compliance to the material elements of the specification. Such references should not be construed as a guarantee of compliance to all requirements in a given specification.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

<u>8420-11B1-RK-TP</u>	<u>8452-11B1-RK-TP</u>	<u>8468-21A1-RK-TP</u>	<u>8468-21B1-RK-TP</u>	<u>8484-21A1-RK-TP</u>	<u>8452-21A1-RK-TP</u>
<u>8420-21B1-RK-TP</u>	<u>8432-21B1-RK-TP</u>	<u>8444-21A1-RK-TP</u>	<u>8432-21A1-RK-TP</u>	<u>8452-21B1-RK-TR</u>	<u>8468-21B1-RK-TR</u>